# Ceiling lampholders

## Medium base ceiling lampholders

### **Product description**

Medium base 660W, 125V/AC 660W, 250V/AC

#### **Features**

- Mounts on 4" (101.6mm) outlet boxes with breakout for 3.25" (82.5mm) box mounting
- Leads are 6" (152.4mm) 221°F (105°C) insulated stranded #16, stripped 0.75" (19.0mm)
- Pull chain devices include ball chain, 3' (0.9m) of cord, connector and end bell
- Top wire versions have terminal screws backed out - ready for wiring - without removing interior
- · Push wire terminals are top wired with two push-in terminals and two screw terminals for continuous wiring
- Plastic models made with high-temperature thermoset plastic to reduce breakage
- Porcelain models made with high-strength insulator porcelain; pull chain versions feature removable interiors











## Plastic ceiling lampholders



UL us 4	12
---------	----

Rating					<b>*</b>
W	V/AC	Description	Color	Catalog no.	<b>♣</b> €
660	250	Two piece, push wire/top wire, pull chain switch	W	☐ S759W-CD	•
		Two piece, 6" (152.4mm) leads, pull chain switch	W	□ S788W	•
		Two-piece, with 15A 125V/AC NEMA 1-15P 2P, 2W outlet push wire/top wire, pull chain switch	W	□ S860W	•
		Two-piece, with 15A 125V/AC NEMA 1-15P 2P, 2W outlet push wire/top wire, pull chain switch	W	□ S865W	•
		One piece, 4 top wire screws, keyless switch	W	□ S1174W	• •
		One piece, 6" (152.4mm) leads, keyless switch	W	□ S1174-6W*	• •
		Two piece, push wire/top wire, keyless switch	W	□ S768W	•
		Two piece, 6" (152.4mm) leads, keyless switch	W	□ S768-6W*	•
v					

<sup>\*</sup> Not cULus Listed & NOM certified

## Porcelain ceiling lampholders





ng				
V/AC	Description	Color	Catalog no.	RoHS
125	Two piece, w/ 15A 125V/AC 2P 2W outlet, 2 screw terminals, top wire, pull chain switch	W	□ 669	•
	Two piece, w/ 15A 125V/AC 2P 3W outlet, 2 screw terminals, top wire, pull chain switch	W	□ 667	•
250	One piece, w/ feed-through, 4 screw terminals, top wire, keyless switch	W	□ 604	•
	Two piece, w/ feed-through, 4 screw terminals, top wire, pull chain switch	W	□ 659	•
		Two piece, w/ 15A 125V/AC 2P 2W outlet, 2 screw terminals, top wire, pull chain switch  Two piece, w/ 15A 125V/AC 2P 3W outlet, 2 screw terminals, top wire, pull chain switch  One piece, w/ feed-through, 4 screw terminals, top wire, keyless switch  Two piece, w/ feed-through, 4 screw terminals, top wire,	Two piece, w/ 15A 125V/AC 2P 2W outlet, 2 screw terminals, top wire, pull chain switch  Two piece, w/ 15A 125V/AC 2P 3W outlet, 2 screw terminals, top wire, pull chain switch  One piece, w/ feed-through, 4 screw terminals, top wire, keyless switch  Two piece, w/ feed-through, 4 screw terminals, top wire, W	Two piece, w/ 15A 125V/AC 2P 2W outlet, 2 screw terminals, top wire, pull chain switch  Two piece, w/ 15A 125V/AC 2P 3W outlet, 2 screw terminals, top wire, pull chain switch  W G667  W G667  Une piece, w/ feed-through, 4 screw terminals, top wire, keyless switch  Two piece, w/ feed-through, 4 screw terminals, top wire, W G59

#### **Color information:**

W (White)



Compliances, specifications and availability are subject to change without notice.



