

Eaton 604812-12FD

Catalog Number: 604812-12FD

Eaton B-Line series ground mounted panel enclosure, 60" height, 12" length, 48" width, NEMA 12, Hinged cover, 12FD enclosure, Ground mount, Large double door, Ground mount legs, Carbon steel, Oil-resistant gasket



General specifications

Product Name	Catalog Number
Eaton B-Line series type 12 panel enclosures	604812-12FD
	UPC
	782051807608
Product Length/Depth	Product Height
12 in	60 in
Product Width	Product Weight
48 in	329.7 lb
Certifications	
UL 508A	
CSA C22.2.	
NEMA	

Material/finish

Material

Carbon steel

Wall thickness

12 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Large double door

Model

12FD enclosure

Cover type

Hinged

Mounting method

Ground

Mounting hole details

Ground mount legs

Locking provisions

Key lock padlock provision

Closure type

Hinged

Special features

Plated door clamps

Standards

NEMA Rating

12

Country of origin

US

Resources

Catalogs

[Electrical Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 604812-12FD](#)