



Wire Bending Cabinet Tip Screwdriver 4-Inch



Wire Bending Cabinet-Tip Screwdriver with Round Shank. Metal stud offers a convenient and easy way to bend, loop, and connect solid wire when installing outlets and switches. 1/4-Inch shank tip width and a 4-Inch shank. Cushion Grip handle allows for greater torque and comfort. Integral flanges inside handle provide solid, twist resistant blade anchor. Special heat treated shafts. Precision machined tip for exact fit. Premium chrome plated for smooth feel and corrosion resistance. Patented Tip-Ident quickly identifies the type of screwdriver and screwdriver tip orientation. Meets or exceeds applicable ASME / ANSI specifications.

Specifications

Bends:	AWG Gauges Nos. 10, 12, 14	Tip Type:	Cabinet
Magnetic:	No	Tip Size:	1/4" (6.4 mm)
Shank Type:	Round	Shank Length:	4" (10.2 cm)
Insulated:	No	Overall Length:	8.344" (21.2 cm)
Weight:	4 oz (113 g)		