

Bulb Shape	Base	Watts	Order Code	Description	Volts	Case Qty	Filament Design	MOL (in)	LCL (in)	Rated Life (hrs)	Lumens Initial	Color Temp K	CBCP	Beam Spread	Warning and Caution Notices	Reduced Wattage	Additional Information
Incandescent Lamps (continued)																	
50 Watts (continued)																	
R20	Med	50	14888	50R20/PL/1-6PK	120	30	CC-6	3.93		2000					2a, 5e, 9k		Reflector Plant Light
R20	Med	50	22752	50R20/BLB 6PK	120	6	CC-6	3.93		1000					2a, 2f, 5b, 7a, 7c, 9k		Blacklight Reflector
		50	46854	50R20/HP/1	120	30	CC-6	3.93		2000					2a, 5e		Reflector, Hot Pink
		50	48038	50R20/FUS 130V	130	30	CC-6	3.93		2000					2a, 5e		Reflector, Fusia
T12	Med	50	16726	50/50T12	115	24	C-5/C-9	5.31	3.00	750	400						Clear-2-filament Marine Running Light, BB
50/100/150 Watts																	
A21	Med	50/100/150	97494	50/150-1PK	120	12	CC-8	5.25	3.88	1200	615/1540/2155				2b, 9j		Soft-White, 3-Way
		50/100/150	97763	50/150-2PK	120	6	CC-8	5.25	3.88	1200	615/1540/2155				2b, 9j		Soft-White, 3-Way
		50/100/150	97785	50/150RVL-1/12PQ	120	12	CC-8	5.25	3.88	1200	450/1150/1600				2b, 9j		Reveal®, Soft-White 3-Way
		50/100/150	97469	50/150/RVL-2PK	120	6	CC-8	5.25	3.875	1200	450/1150/1600				2b, 9j		Reveal®, Soft-White 3-Way
		50/100/150	97781	50/150/LL-1/12PK	120	12	CC-8	5.25	3.87	2400	500/1350/1850				2b, 9j		Long Life, Soft-White 3-Way
50/200/250 Watts																	
A21	Med	50/200/250	97482	50/250/1-1PK	120	12	CC-8/CC-25	5.25	3.87	1200	620/3335/3955				2b, 9c, 9j		Soft-White, 3-Way
52 Watts																	
A19	Med	52/46	97849	60A/52WM-130V	130/120	24	CC-8	4.43	3.12	1000/2600	710/530					↗	Watt-Miser® Diffuse Coating
57 Watts (Complies with California Title 20 Regulations)																	
A19	Med	57	71909	57A 48PK	120	144	CC-6	4.43	3.12	1000	780					↗	Inside Frost
		57/50	71951	57A/130V-4PK	130/120	144	CC-8	4.43	3.12	1200/3200	760/570					↗	Inside Frost
		57	71959	57A/W-4PK	120	144	CC-6	4.43	3.12	1000	770					↗	Soft-White
		57	71979	57A/CL-2/12PK	120	24	CC-6	4.43	3.12	1000	790					↗	Clear
		57/50	72248	57A/CL/2PK-130V	130/120	24	CC-8	4.43	3.12	1200/3200	760/575					↗	Clear
		57	71970	57A/W/LL50-2PK	120	24	CC-8	4.43	3.12	1500	765					↗	Soft-White, Long Life
60 Watts																	
A19	Med	60	97490	60A/CL-2PK	120	24	CC-6	4.43	3.12	1000	870						Clear
		60	41026	60A 48PK	120	144	CC-6	4.43	3.12	1000	865						Standard
		60	41028	60A/W 48PK	120	144	CC-6	4.43	3.12	1000	840						Soft-White
		60	48688	60A/RVL 48PK	120	144	CC-8	4.43	3.12	1000	630						Reveal® Soft-White
		60	73188	60A/CL/RVL-PK24	120	120	CC-6	4.43	3.12	1000	650						Reveal® Clear
		60	97496	60A/W/LL-2PK	120	24	CC-6	4.43	3.12	1500	820						Soft-White
		60	22361	60A/COMM 24PK	120	24	CC-6	4.43	3.12	1000	855						Inside Frost
		60/53	72529	60A/RS130-PK2/12	130/120	24	C-7A	4.13	2.91	2000/5400	500/380				2a, 5e		Rough Service
		60/53	72549	60A/RS/STG-T2/12	130/120	24	C-7A	4.13	2.91	2000/5400	500/380				2a		Rough service Saf-T-Gard®
		60	97483	60A/SPK-2PK	120	24	CC-6	4.43	3.12	1000	675				2b		Pink
		60	72816	60A/SPK-2/10PK	120	20	CC-6	4.43	3.12	1000	675				2b		Soft Pink
		60	97495	60A/Y-2PK	120	24	CC-6	4.43	3.12	1000	550						Yellow-Bug Light
		60	25905	60A/BLB 6PK	120	30	C-9	4.43		1000					2a, 2f, 5b, 7a, 7c, 9k		Blacklight
		60	73277	60A/BLB/TW-6PK	120	6	C-9	4.43	3.12	1000					2a, 2f, 5b, 7a, 7c, 9k		Blacklight
		60	73181	60A/NET-6PK	120	6	CC-8	4.44	3.13	1000							
		60	41624	60A/PL 6PK	120	30	CC-6	4.43	3.12	1000	630				5e		Plant
A15	Med	60	17759	60A15/CF CD2	120	60	C-9	3.50	2.37	1500	650						Clear-Ceiling Fan and Appliance, Vibration Resistant
		60	47259	60A15/CF/CD4-6PK	120	30	C-9	3.50	2.38	1500	650						Clear, Ceiling Fan
		60	14029	60A15/W/CF-CD2	120	60	C-9	3.50	2.37	1500	650						White-Ceiling Fan, Vibration Resistant
		60	73186	60A15/CF/RVL/CD2-6PK	120	6	C-9	3.50	2.38	1500	480						Reveal® Ceiling Fan, Vibration Resistant
		60	73182	60A15/W/CF/RVL/CD2-6PK	120	6	C-9	3.50	2.38	1500	465						Reveal®, Soft-White
		60	46888	60A15CF/STGPQ2/6	120	30	C-9	3.50	2.37	1500	650				9l		Ceiling Fan Saf-T-Gard®