



GE  
Lighting

### 76231 - GE crystal clear 60 watt bent tip 4-pack

#### 60CAM/CL/CD4-MPD

- ☞ 2500K soft white light appearance
- ☞ Add sparkle to your decorative fixtures with GE crystal clear bulbs. The clear glass and elegant filament design provide a decorative touch in fixtures where the bulb is visible. GE crystal clear decorative bulb shape compliments fixtures where the bulb is visible, like sconces and chandeliers
- ☞ Bent Tip candle with medium base for use in chandeliers and sconces
- ☞ Estimated yearly energy costs \$7.23 based on 3 hours per day \$0.11 per kWh
- ☞ Lasts 1.4 years based on 3 hours per day usage
- ☞ 600 lumens providing cozy, relaxing™ light

#### Product Photo



#### GENERAL CHARACTERISTICS

|                          |                       |
|--------------------------|-----------------------|
| Base Description         | Medium Screw          |
| Base Material            | Aluminium             |
| Base Type                | Screw-In              |
| Bulb Finishes and Colors | Crystal Clear         |
| Filament                 | CC-2V                 |
| Life in Years            | 1.4 yr                |
| Rated Life Hours-nominal | 1500 h                |
| Primary Application      | Standard <Decorative> |
| Bulb Material            | Soft glass            |
| Product Technology       | Incandescent          |
| Base                     | E26                   |
| Bulb Shape               | CA10                  |

#### PHOTOMETRIC CHARACTERISTICS

|                                |        |
|--------------------------------|--------|
| Nominal Initial Lumen per Watt | 9      |
| Initial Lumens-nominal         | 600 lm |
| Color Temperature              | 2500 K |

#### PRODUCT INFORMATION

|                             |                  |
|-----------------------------|------------------|
| Product Code                | 76231            |
| Description                 | 60CAM/CL/CD4-MPD |
| Alternative Unit Of Measure | CASE             |

#### DIMENSIONS

|          |         |
|----------|---------|
| Diameter | 1.25 in |
|----------|---------|

#### ELECTRICAL CHARACTERISTICS

|                                |         |
|--------------------------------|---------|
| Wattage                        | 60 W    |
| Estimated Energy Cost per Year | 7.23 \$ |
| Input Voltage [nom]            | 120 V   |