



**Product Number:** 14262

**Order Abbreviation:** 60G25/W/RP 120V 6/CS 1/SKU

**General Description:** Incandescent G25 Décor Bulb Shape Soft White Finish Medium Aluminum Base 60Watt  
120Volt Retail Pack 6Bulbs Per Case 1Bulb Per Package

**\* Full Case Required**

#### Product Information

Abbrev. With Packaging Info.	60G25WRP 120V 6/CS 1/SKU
Approx. Lumens	475
Average Rated Life (hr)	1500
Base	Medium
Bulb	G25
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	3.125
Diameter (mm)	79.38
Filament	C-9
Lamp Finish	Soft White
Maximum Overall Length - MOL (in)	4.438
Maximum Overall Length - MOL (mm)	112.7125
Nominal Voltage (V)	120.00
Nominal Wattage (W)	60.00

