

Incandescent Lamps

Bulb Shape	Base	Watts	Order Code	Description	Volts	Case Qty	Filament Design	MOL (in)	LCL (in)	Rated Life (hrs)	Lumens Initial	Color Temp K	CBCP	Beam Spread	Warning and Caution Notices	Reduced Wattage	Additional Information
Incandescent Lamps (continued)																	
60 Watts (continued)																	
A15	Cand	60	71395	60A15/CA/C/CF-CD2	120	6	C-7A	3.50	2.37	1500							Clear-Ceiling Fan, Vibration Resistant
		60	71396	60A15/CA/W/CF-CD2	120	6	C-7A	3.50	2.37	1500							White-Ceiling Fan, Vibration Resistant
T10	Med	60	45141	60T10 CD1-5PK	120	25	C-8	5.63		1000	740						Clear-Display Light
		60	17292	60T10/64 24PK	120	192	C-8	5.62		1000	740						Clear-Showcase, BDTH
		60	48710	60T10/RVL CD1	120	25	C-8	5.63		1000							Reveal® - Clear
R46	Scr w Term	60	17212	60PAR/2/R	38	12	CC-2V	3.75		800							Red Lens - Train Warning
65 Watts																	
BR30	Med	65	18011	65R/FL/MI-TWIN	120	6	CC-6	5.37		2000	755				2a, 5e, 9k	✖	Reflector Flood Twin Pink
		65	20331	65R30/FL/MI- 6PK	120	30	CC-6	5.37		2000	755				2a, 5e, 9k	✖	Reflector Flood
		65	20332	65R30/SP/MI-6PK	120	30	CC-6	5.37		2000	755				2a, 5e, 9k	✖	Reflector
		65	22714	65R30FL/COMM12PK	120	12	CC-6	5.37		2000	770				2a, 5e, 9k	✖	Reflector Flood 12 Pack
		65	26805	65R30/FL/LL 6PK	120	30	CC-6	5.37		2500	725				2a, 5e, 9k	✖	Long Life Reflector-Flood
		65	48917	65R30/FL/LLPQ2/3	120	15	CC-6	5.37		2500	725				2a, 5e, 9k	✖	Long Life Indoor Floodlight
		65	26806	65R30/SP/LL 6PK	120	30	CC-6	5.37		2500	725				2a, 5e, 9k	✖	Long Life Spotlight
		65	73183	65R30/FL/RVL-6PK	120	6	CC-6	5.37		2000					2a, 2b, 5e, 9k	✖	Reveal® Floodlight
		65	73179	65R30/RVL/TW-3PK	120	3	CC-6	5.37		2000					2a, 2b, 5e, 9k	✖	Reveal® Floodlight
		65	47723	65R30FL/STGPQ1/6	120	30	CC-6	5.37		2000					2a, 2b, 5e, 9k, 9a, 9l	✖	Indoor Flood Light-Saf-T-Gard®
		65	41837	65R30/SP/HP	120	30	CC-6	5.37		2000					2a, 5e, 9k		Indoor Reflector, Hot Pink
		65	26803	65R30/FL/PK	120	30	CC-6	5.37		2000					2a, 5e, 9k	✖	Reflector - Pink
		65	26641	65R30/FL/B	120	30	CC-6	5.37		2000					2a, 5e, 9k	✖	Reflector - Blue
		65	26642	65R30/FL/G	120	30	CC-6	5.37		2000					2a, 5e, 9k	✖	Reflector - Green
		65	26645	65R30/FL/Y	120	30	CC-6	5.37		2000					2a, 5e, 9k	✖	Reflector - Yellow
		65	20996	65R30/PL-1 6PK	120	30	CC-6	5.37		2000					2a, 5e, 9k	✖	Reflector-Plant Light, BB
		65	46855	65R30/FL	130	30	CC-6	5.37		2000	725				2a, 2b, 5e, 9k	✖	Watt-Miser® Reflector
		65	46856	65R30/SP	130	30	CC-6	5.37		2000	725				2a, 2b, 5e, 9k	✖	Watt-Miser® Reflector
		65	46857	65R30/FL/PK	130	30	CC-6	5.37		2000					2a, 2b, 5e, 9k	✖	Watt-Miser® Reflector-Pink
		65	48039	65R30SP/FUS 130V	130	30	CC-6	5.37		2000					2a, 2b, 5e, 9k	✖	Indoor Reflector, Fusia
BR40	Med	65	14016	65R40/FL/MI-6PK	120	30	CC-6	6.56		2000	730				2a, 2b, 5e, 9k		Reflector Flood
		65	47683	65R40/FL/LL	120	30	CC-6	6.56		2500	650				2a, 2b, 5e, 9k		Long Life Reflector-Indoor Floodlight
		65	46861	65R40/FL	130	30	CC-6	6.56		2000	700				2a, 2b, 5e, 9k		Watt-Miser® Reflector-LF
BR40	Med	65	87904	65R40FL/RVL-TP6	120	30	CC-6	6.56		2000					2a, 2b, 5e, 9k		Reveal® Reflector Flood
PAR38	Med Sid Pr	65	80314	75PAR/3FL/65WWM	120	12	CC-6	4.3		2000	675	2675	1750	30	1a,2a,2b	✖	Compact Flood
67 Watts																	
A19	Med	67/60	97850	75A/67WM-130V	130/120	24	CC-8	4.43	3.12	1000/2600	1000/755					✖	Inside Frost
69 Watts																	
A21	Med	69	17325	69A21/TS	130	120	C-9	4.37	2.43	8000	675					✖	Clear-Traffic Signal, BDTH
71 Watts (Complies with California Title 20 Regulations)																	
A19	Med	71	71910	71A 48PK	120	144	CC-6	4.43	3.12	750	1075					✖	Inside Frost
		71/63	71952	71A/130V-4PK	130/120	144	CC-8	4.43	3.12	750/1950	1050/790					✖	Inside Frost
		71	71960	71A/W-4PK	120	144	CC-6	4.43	3.12	750	1060					✖	Soft-White
		71	71980	71A/CL-2/12PK	120	24	CC-6	4.43	3.12	750	1090					✖	Clear
		71	71971	71AW/LL50-2PK	120	24	CC-8	4.43	3.12	1125	1055					✖	Soft-White, Long Life