

NEW!
More on
reverse

Low Profile IN and OUT[®] Cover

Low Profile when not in use • Extra Duty Weatherproof in use Cover

IN for
GOOD LOOKS!



OUT
to PLUG IN



Paintable
White Cover
VERTICAL
Standard size
60WW

TO CLOSE
Bow out the
sides of the extended
cover and Push IN



Arlington's non-metallic **IN** and **OUT[®]** **Cover** is a low profile cover when *not in use*, and a deep, extra duty weatherproof in use cover when a cord's plugged in!

IN, cord holes seal the box to keep bugs out. It extends quickly and easily into the **OUT** position to accommodate a plug – then back to a low profile cover when closed.

- Covers fit over any box or opening in new or existing projects - *Cover is removable for easier device installation*

- **Two sizes** in Vertical and horizontal styles
60 series fits over standard openings.
61 series with installed oversized base, covers large openings or a round 3.5" outlet box.

- **Cover colors** Paintable white or clear
- Installed gaskets
- UV rated plastic for long outdoor life
- Listed weatherproof in use installation – Meets NEC Section 406.9 (B), for the protection of exterior outlets where an extra duty weatherproof in use cover is required for 15 or 20 AMP receptacles installed outdoors

Patented
Additional patents pending



Arlington[®]

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717 • Fax 570/562.0646
www.aifittings.com

Vertical and Horizontal IN and OUT[®] Cover

Fits over All Boxes and Openings in New or Old Work

Fast, Easy Installation



- 1 Feed device through opening.
* cover is removable for easier access




- 2 Install wiring device per manufacturer's instructions, and Local and National Electrical Codes using the pre-drilled holes in the base.



- 3 Install the plate and the installation is done!

IN and OUT Covers for Standard Boxes



for Oversized Openings or 3.5" Round Boxes

Horizontal
61HW
not shown



Catalog Number	UPC/DEI/NAED Mfg. #018997	Cover Orientation/Color IN and OUT COVER	Base Size	Unit Pkg	Std Pkg
60VW	00680	Vertical • White	Standard	1	4
61VW	00681	Vertical • White	Oversized	1	4
60VC	00682	Vertical • Clear	Standard	1	4
61VC	00683	Vertical • Clear	Oversized	1	4
60HW	00684	Horizontal • White	Standard	1	4
61HW	00685	Horizontal • White	Oversized	1	4
60HC	00686	Horizontal • Clear	Standard	1	4
61HC	00687	Horizontal • Clear	Oversized	1	4

Includes low profile cover, (1) standard duplex and (1) standard GFCI face plate, installation screws, installed gaskets

IN and OUT Covers
Meet NEC Section 406.9 (B)
for the protection of exterior outlets where an extra duty weatherproof in use cover is required for 15 or 20 AMP receptacles installed outdoors.



Distributed by



Arlington[®]

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717 • Fax 570/562.0646
www.aifittings.com

Patented. Additional patents pending

IN&OUT COVER 0806 REV 1008, 0325/7500

NEW!
More on
reverse

Low Profile IN and OUT[®] Cover

Low Profile when not in use • Extra Duty Weatherproof in use Cover

IN for
GOOD LOOKS!



OUT
to PLUG IN



Paintable
White Cover
VERTICAL
Standard size
60WW

TO CLOSE
Bow out the
sides of the extended
cover and Push IN



Arlington's non-metallic **IN** and **OUT[®]** **Cover** is a low profile cover when *not in use*, and a deep, extra duty weatherproof in use cover when a cord's plugged in!

IN, cord holes seal the box to keep bugs out. It extends quickly and easily into the **OUT** position to accommodate a plug – then back to a low profile cover when closed.

- Covers fit over any box or opening in new or existing projects - *Cover is removable for easier device installation*

- **Two sizes**
in Vertical and horizontal styles
60 series fits over standard openings.
61 series with installed oversized base, covers large openings or a round 3.5" outlet box.

- **Cover colors** Paintable white or clear
- Installed gaskets
- UV rated plastic for long outdoor life
- Listed weatherproof in use installation – Meets NEC Section 406.9 (B), for the protection of exterior outlets where an extra duty weatherproof in use cover is required for 15 or 20 AMP receptacles installed outdoors

Patented
Additional patents pending



Arlington[®]

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717 • Fax 570/562.0646
www.aifittings.com

Vertical and Horizontal IN and OUT[®] Cover

Fits over All Boxes and Openings in New or Old Work

Fast, Easy Installation



- 1 Feed device through opening.
* cover is removable for easier access




- 2 Install wiring device per manufacturer's instructions, and Local and National Electrical Codes using the pre-drilled holes in the base.




- 3 Install the plate and the installation is done!

IN and OUT Covers for Standard Boxes



for Oversized Openings or 3.5" Round Boxes

Horizontal
61HW
not shown



Catalog Number	UPC/DEI/NAED Mfg. #018997	Cover Orientation/Color IN and OUT COVER	Base Size	Unit Pkg	Std Pkg
60VW	00680	Vertical • White	Standard	1	4
61VW	00681	Vertical • White	Oversized	1	4
60VC	00682	Vertical • Clear	Standard	1	4
61VC	00683	Vertical • Clear	Oversized	1	4
60HW	00684	Horizontal • White	Standard	1	4
61HW	00685	Horizontal • White	Oversized	1	4
60HC	00686	Horizontal • Clear	Standard	1	4
61HC	00687	Horizontal • Clear	Oversized	1	4

Includes low profile cover, (1) standard duplex and (1) standard GFCI face plate, installation screws, installed gaskets

IN and OUT Covers
Meet NEC Section 406.9 (B)
for the protection of exterior outlets where an extra duty weatherproof in use cover is required for 15 or 20 AMP receptacles installed outdoors.



Distributed by



Arlington[®]

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717 • Fax 570/562.0646
www.aifittings.com

Patented. Additional patents pending

IN&OUT COVER 0806 REV 1008, 0325/7500