

# COPPER-BONDED GROUND ROD, POINTED, 3/4" DIA, 10', 10 MIL PLATING, 12.6 LB

### **CATALOG NUMBER**

# 613400



#### **CERTIFICATIONS**









## **FEATURES**

99.9% pure electrolytic copper coating

Rods have a high carbon steel core and tip that provide superior strength when driving

Copper coating will not crack when bent or tear when driven

Minimum copper coating of 10 mils on rods listed to UL® 467

nVent ERICO name, length, diameter and part number is roll-stamped within 12" (304,8 mm) of chamfered end

UL logo and control number where applicable stamped on each rod for easy inspection after installation

# PRODUCT ATTRIBUTES

Material: Copper-Bonded Steel

Tensile Strength: 80,000 psi Min

Ground Rod Diameter, Nominal: 3/4"

Ground Rod Diameter, Actual: 0.681"

Length: 10'

Plating Thickness: 10 mil

Unit Weight: 12.600 lb

UPC Label: No

Complies With: IEC® EN 62561-2;ANSI®/NEMA® GR1


## **ADDITIONAL PRODUCT DETAILS**

For rods to be listed to UL® 467, they must be at least 8' (2.44 m) in length.

IEC® EN 62561-2 supercedes EN 50164-2.

Additional lengths available.

## **DIAGRAMS**



#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

## North America

+1.800.753.9221

Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe** 

Germany: 800 1890272

Other Countries:

+31 13 5835404

**APAC** 

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

