

Enduro® Headlamp

Case Material: Impact resistant ABS case available in black, REALTREE Hardwoods® Green High Definition® (HD) camo pattern, or REALTREE Hardwoods® Blaze

Dimensions: Facecap Diameter: 1.3 in. (3.25 cm) Maximum Width: 2.25 in. (5.7 cm)
Maximum Depth: 1.6 in. (4.0 cm) including headstrap & mounting plate

Weight: 2.75 oz (78.5 grams)* with batteries and strap

Lens: Unbreakable polycarbonate lens.

Light Source: 0.5 Watt High-Flux LED; 30,000 hours rated LED life
Nichia Ultra-Bright Green LED; 50,000 hours rated LED life

Light Output: 0.5W LED (White): 850 Candela Peak Beam Intensity; 14.5 Lumens
Measured System Output (High Mode)
6 Lumens Measured System Output (Low Mode).

Nichia Ultra-Bright (Green): 162 Candela Peak Beam Intensity;
8 Lumens Measured System
Output (High Mode) and 4 Lumens Measured System Output (Low Mode)

On/Off: Pushbutton – 1st mode = Low; 2nd mode = High

Run Time: 0.5W High-Flux LED (White) Black and REALTREE HARDWOODS Green HD models only.
Up to 6 continuous hours to the 10% lumen output level (High Mode)
Up to 12 continuous hours to the 10% lumen output level (Low Mode)

Nichia Ultra-Bright (Green) – REALTREE HARDWOODS Blaze model only.
Up to 9 continuous hours to the 10% lumen output level (High Mode)
Up to 120 continuous hours to the 10% lumen output level (Low Mode)

Battery: Two (2) “AAA” alkaline batteries.

- Features:**
- Securely clips to the brim of your hat for convenient, hands-free use
 - O-ring sealed construction - Waterproof to 1M for 1 hour
 - Super high-flux LED - reflector focused for 100 ft + range
 - Solid State Power Regulation provides maximum light output throughout battery life
 - Impact resistant housing - drop test verified

Approvals: Most models meet applicable European Community Directives

Warranty: Limited lifetime warranty

**With batteries (included in purchase).
Made in China*



Item		UPC	Part #
Enduro	Black	080926-61400-0	61400
Enduro	Camo	080926-61405-5	61405
Enduro	Blaze Orange Camo	080926-61407-9	61407

