

COPPER-BONDED GROUND ROD, POINTED, 5/8" DIA, 8', 10 MIL PLATING, 6.8 LB

CATALOG NUMBER

615880



CERTIFICATIONS



FEATURES

99.9% pure electrolytic copper coating

Rods have a high carbon steel core and tip that provide superior strength when driving

Copper coating will not crack when bent or tear when driven

Minimum copper coating of 10 mils on rods listed to UL® 467

nVent ERICO name, length, diameter and part number is roll-stamped within 12" (304,8 mm) of chamfered end

UL logo and control number where applicable stamped on each rod for easy inspection after installation

PRODUCT ATTRIBUTES

Material: Copper-Bonded Steel

Tensile Strength: 80,000 psi Min

Ground Rod Diameter, Nominal: 5/8"

Ground Rod Diameter, Actual: 0.560"

Length: 8'

Plating Thickness: 10 mil

Unit Weight: 6.800 lb

UPC Label: No

Complies With: IEC® EN 62561-2;ANSI®/NEMA® GR1


ADDITIONAL PRODUCT DETAILS

For rods to be listed to UL® 467, they must be at least 8' (2.44 m) in length.

IEC® EN 62561-2 supercedes EN 50164-2.

Additional lengths available.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

Our powerful portfolio of brands: CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER nVent.com

nVent reserves the right to change specifications without notice.