

ETP Steel EMT Compression Couplings

6000S Series Couplings

Application

- To ground and secure EMT raceway sections together.

Feature

- Concretetight.
- Raintight (wet locations) Canada.

Material/Finish

- Body and nut: steel
- Steel/zinc plated

Certifications and Compliances

- UL Standard: 514B
- UL Listed: E14895
- cUL Listed: E14895, E14815
- CSA Certified: 009795 • NEMA: FB-1

6000US Series Couplings

Application

- To ground and secure EMT raceway sections together.

Feature

- Made in the U.S.A.
- Concretetight.
- Raintight (wet locations) Canada.

Material/Finish

- Body and nut: steel
- Steel/zinc plated

Certifications and Compliances

- UL Standard: 514B
- UL Listed: (1/2 - 3) E14815
- CSA Standard: C22.2 No. 18.3
- cUL Listed: (1/2 - 3) E14815
- NEMA: FB-1



6050S – 6400S



6050US – 6200US



6250US – 6400US

Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters		Weight Lbs./Kgs. Per 100
		Body Length	Maximum Diameter	
1/2	6050S	1.38/35.1	0.84/21.3	19.00/8.62
3/4	6075S	1.50/38.1	1.38/35.1	25.00/11.34
1	6100S	1.66/42.2	1.31/33.3	39.00/17.69
1-1/4	6125S	2.50/63.5	1.69/42.9	88.00/39.92
1-1/2	6150S	2.50/63.5	1.94/49.3	104.00/47.17
2	6200S	2.50/63.5	2.38/60.5	149.00/67.59
2-1/2 *	6250S	4.25/108.0	3.13/79.5	240.00/108.86
3 *	6300S	4.50/114.3	3.75/95.3	350.00/158.76
3-1/2 *	6350S	4.75/120.7	4.25/108.0	475.00/215.46
4 *	6400S	5.00/127.0	4.75/120.7	600.00/272.16

Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters	
		Body Length	Maximum Diameter
1/2	6050US	1.34/34.0	0.97/24.6
3/4	6075US	1.34/34.0	1.22/31.0
1	6100US	1.41/35.8	1.50/38.1
1-1/4	6125US	1.75/44.5	1.91/48.5
1-1/2	6150US	1.88/47.8	2.16/54.9
2	6200US	2.13/54.1	2.69/68.3
2-1/2	6250US	5.50/139.7	4.13/104.9
3	6300US	5.50/139.7	4.69/119.1
3-1/2	6350US	5.63/143.0	5.34/135.6
4	6400US	5.75/146.1	5.88/149.4

* Rated for steel EMT, aluminum and steel RMC, and steel IMC.