



62027

F96T12 D/HO-O/ALTO/TSC (PK X 15)



Application: Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

Base: Recessed Double Contact (R17d)

Coating: Copolymer

Color Temperature: 6500 K

Diameter: 1.50 IN

Lamp Type: Fluorescent

Mean Design Lumens: 6800

Package Weight: 22.85 L

Shape: T

Type: Straight Linear Fluorescent Lamp

Wattage: 110.0 W

Average Life Hours: 14000

Bulb: T12

Color: Daylight

CRI: 79

Initial Lumens: 7800

Length: 96.00 IN

Package (LxWxH): 96.25 IN x 8.75 IN x 5.25 IN

Pack By: 15

Special Features: Shatter-Resistant

UPC: 726585620272

ULEPH,ROHS,NSF Splash Zone