

Project Name

Location

Prepared By



NUVO 62-1144R1

2 LT LED LG UP & DOWN SCONCE

Notes

[www] 06-27-2021 00:19:09

General

Status	Active
Finish	Black
Wattage	20W
Style	Utility
CCT (Kelvin)	3000
Color Temperature	Warm White
Length (in.)	3.16
Width (in.)	5.00
Height (in.)	11.75
Extension (in.)	4.22
Indoor or Outdoor Fixture	Outdoor

Specifications

Technology	LED
CRI	90
Lumen Output	1800L
Rated Hours	50000
Voltage	120V/277V
Dimmable	Non-Dimmable
Weight (lb.)	2.51
Up/Down Installation	Up/Down
Fixture Material	Die Cast Aluminum
Fixture Type	Sconce
Operating Temperature	-30C (-22F) to a maximum of +50C (+122F)

Dimensions

Back Plate or Canopy Length (in.)	4.50
Back Plate or Canopy Width (in.)	4.50

Compliance

Safety Listing	cULus
Location Rating	Wet
UL Application	Outdoor
Energy Star	Yes
ES Unique ID	ESID-2336402
ADA Compliant	No
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Installation Notes	Mounts Up and Down
Warranty	5 Year Limited - Fixtures