

Project Name

Location

Prepared By



Notes

[www] 01-15-2024 02:40:00

General

Status	Discontinued
Substitute	62-1801
Finish	White
Wattage	13W
Style	Transitional
CCT (Kelvin)	3000K/4000K/5000K
Color Temperature	Warm to Cool White
Width (in.)	7.4
Height (in.)	1.28
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	No
-------------	----

Specifications

Technology	LED
CRI	90
Lumen Output	930L-1070L
Rated Hours	50000
Voltage	120V
Dimmable	Yes-Dimmable
Fabric Description	Frosted
Weight (lb.)	0.76
Sloped Ceiling	Yes
Fixture Shape	Round
Fixture Material	Steel
Fixture Type	Disk Light
Operating Temperature	-35C (-31F) to +50C (+122F)

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2399495
DLC Approved	No
NSF Approved	No
CA T20 / T24 Rationale	California T24 2016 - 2022 JA8 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
California Prop 65	Lead
NEC Compliance	Clothes Closet Certified - Reg: 410.16 (A)(3) and 410.16 (C)(5)
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Specification Note	3000K = 930L; 4000K = 1070L; 5000K = 980L
Warranty	5 Year Limited - Fixtures

