

Project Name

Location

Prepared By



NUVO 62-1803

7" LED DISK LIGHT BRONZE FINIS

Notes

[www] 05-04-2023 07:40:39

General

Status	Active
Finish	Bronze
Wattage	15W
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Color Temperature	Warm to Cool White
Width (in.)	7.42
Height (in.)	1.42
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	No
-------------	----

Specifications

Technology	LED
CRI	93
Lumen Output	780L-910L
Rated Hours	50000
Voltage	120V
Dimmable	Yes-Dimmable
Weight (lb.)	0.58
Sloped Ceiling	Yes
Fixture Shape	Round
Fixture Material	Steel
Fixture Type	Disk Light
Operating Temperature	-25C (-13F) to +40C (+104F)

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2507677
NSF Approved	No
CA T20 / T24 Rationale	California T24 2016 - 2022 JA8 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Installation Notes	Keyhole Slots
Warranty	5 Year Limited - Fixtures