



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Highway 155
75803-8616, TX Palestine
Phone: 903-723-2141
Fax: 903-723-1451



63500 8" 5W Led Undercab 3K/4K/5K White

Satco

Catalog Number	63500
Manufacturer	Satco
Description	5 Watt 8-Inch Led White Under Cabinet Light - CCT Selectable - 40000 Hours
Weight per unit	0.5500 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.042
Lamp Included	Integrated
Lamp Type	LED
Material	Aluminum
Reflector Type	Frosted White
Socket Type	Integrated
Voltage Rating	120
Warranty	5 Year Limited - Fixtures
Wattage	5

Material, Color, and Finish

Color	White
Finish	white
Style	Utility

Dimensions and Weight

Height	1
Length	8
Width	3.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Highway 155
75803-8616, TX Palestine
Phone: 903-723-2141
Fax: 903-723-1451

Descriptions

Description	8" 5W LED UNDERCAB 3K/4K/5K WHITE
extra long description	SATCO 63/500 UNDER CAB LED SCCT 8"
Long Description	5 Watt 8-Inch LED White Under Cabinet Light - CCT Selectable - 40000 Hours
Product Type	Under Cab Led SCCT 8" - WH
Special Features	Warranty: 5-Years ; Location Rating: Dry ; NSF Approved: No ; Style: Utility ; JA8 Compliant: True ; Amps: 0.042A ; Incandescent Equivalent: 20W ; Operating Frequency: 50/60Hz ; Power Factor: >0.9 ; Wattage Selectable: False ; Bulb Included: Integrated ; Beam Angle (degree): 105 ; Cct Selectable: True ; Indoor Outdoor: Indoor ; IP Rating: IP20 ; Lens Finish: Frosted White ; Lens Material: Polycarbonate (PC) ; Mounting Procedure: Under Cabinet: Screws ; Operating Temp: -20C (-4F) to +40C (+104F) ; Replaceab

Manufacturer Information

Brand	Nuvo
GTIN	00045923635007
Manufacturers Part Number	63/500
UPC	045923635007

Taxonomies, Classifications, and Categories

Category Description	LED TRACK, RAIL, TASK & UNDERCABINET LIGHTING
Type	Functional Lighting

Packaging

Carton	1
Weight	0.55
Weight Per each	0.55

Uses, Certifications, and Standards

Application	Under Cabinet & Cove
Frequency Rating	50/60
Mounting	Under Cabinet: Screws
Operating Temperature standard	-20C (-4F) to a maximum of +40C (+104F) cETLus - Listed