



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## 63501 11" 7W Led Undercab 3K/4K/5K White

Satco



|                  |  |
|------------------|--|
| Catalog Number   | 63501  |
| Manufacturer     | Satco  |
| Description      | 6.5 Watt 11-Inch Led White Under Cabinet Light - CCT Selectable<br>- 40000 Hours |
| Weight per unit  | 0.9780 (lbs/each)  |
| Product Category | Lighting   |

### Features

|                 |                           |
|-----------------|---------------------------|
| amperage rating | 0.054                     |
| Lamp Included   | Integrated                |
| Lamp Type       | LED                       |
| Material        | Aluminum                  |
| Reflector Type  | Frosted White             |
| Socket Type     | Integrated                |
| Voltage Rating  | 120                       |
| Warranty        | 5 Year Limited - Fixtures |
| Wattage         | 6.5                       |

### Material, Color, and Finish

|        |         |
|--------|---------|
| Color  | White   |
| Finish | white   |
| Style  | Utility |

### Dimensions and Weight

|        |     |
|--------|-----|
| Height | 1   |
| Length | 11  |
| Width  | 3.5 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | 11" 7W LED UNDERCAB 3K/4K/5K WHITE  |
| extra long description | SATCO 63/501 UNDER CAB LED SCCT 11"   |
| Long Description       | 6.5 Watt 11-Inch LED White Under Cabinet Light - CCT Selectable<br>- 40000 Hours  |
| Product Type           | Under Cab Led SCCT 11" - WH   |
| Special Features       | Warranty: 5-Years ; Location Rating: Dry ; NSF Approved: No ;<br>Style: Utility ; JA8 Compliant: True ; Amps: 0.054A ; Incandescent<br>Equivalent: 30W ; Operating Frequency: 50/60Hz ; Power Factor:<br>>0.9 ; Wattage Selectable: False ; Bulb Included: Integrated ;<br>Beam Angle (degree): 105 ; Cct Selectable: True ; Indoor Outdoor:<br>Indoor ; IP Rating: IP20 ; Lens Finish: Frosted White ; Lens<br>Material: Polycarbonate (PC) ; Mounting Procedure: Under<br>Cabinet: Screws ; Operating Temp: -20C (-4F) to +40C (+104F) ;<br>Replaceab |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Nuvo           |
| GTIN                      | 00045923656477 |
| Manufacturers Part Number | 63/501         |
| UPC                       | 045923656477   |

## Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | LED TRACK, RAIL, TASK & UNDERCABINET LIGHTING |
| Type                 | Functional Lighting                           |

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 1     |
| Weight          | 0.71  |
| Weight Per each | 0.978 |

## Uses, Certifications, and Standards

|                                   |  |
|-----------------------------------|--|
| Application                       | Under Cabinet & Cove                                       |
| Frequency Rating                  | 50/60  |
| Mounting                          | Under Cabinet: Screws                                      |
| Operating Temperature<br>standard | -20C (-4F) to a maximum of +40C (+104F)<br>cETLus - Listed |