

Project Name

Location

Prepared By



NUVO 63-502

UNDER CAB LED SCCT 14" - WH

Notes

[www] 11-22-2021 02:57:39

General

| | |
|---------------------------|--------------------|
| Status | Active |
| Finish | White |
| Wattage | 9W |
| CCT (Kelvin) | 3000K/4000K/5000K |
| Color Temperature | Warm to Cool White |
| Length (in.) | 14 |
| Width (in.) | 3.5 |
| Height (in.) | 1 |
| Indoor or Outdoor Fixture | Indoor |

Specifications

| | |
|------------------------|---|
| Technology | LED |
| CRI | 90+ |
| Lumen Output | 577L-647L |
| Rated Hours | 40000 |
| Voltage | 120V |
| Dimmable | Yes-Dimmable |
| Weight (lb.) | 0.87 |
| Sloped Ceiling | No |
| Fixture Shape | Rectangle |
| Fixture Material | Aluminum / Polycarbonate (PC) |
| Fixture Type | Under Cabinet |
| Max. Connectable Units | 48 |
| Operating Temperature | -20C (-4F) to a maximum of +40C (+104F) |

Compliance

| | |
|--------------------|-----------------------|
| Safety Listing | cETLus |
| Location Rating | Dry |
| Energy Star | Yes |
| ES Unique ID | ESID-2384711 |
| California Status | California T24 Listed |
| California Prop 65 | Lead |
| RoHS Compliant | Yes |
| FCC Compliant | Yes |

Additional Information

| | |
|----------|---------------------------|
| Warranty | 5 Year Limited - Fixtures |
|----------|---------------------------|