

Project Name

Location

Prepared By



Notes

[www] 11-22-2021 02:57:39

General

Status	Active
Finish	White
Wattage	17W
CCT (Kelvin)	3000K/4000K/5000K
Color Temperature	Warm to Cool White
Length (in.)	28
Width (in.)	3.5
Height (in.)	1
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
CRI	90+
Lumen Output	1216L-1366L
Rated Hours	40000
Voltage	120V
Dimmable	Yes-Dimmable
Weight (lb.)	1.58
Sloped Ceiling	No
Fixture Shape	Rectangle
Fixture Material	Aluminum / Polycarbonate (PC)
Fixture Type	Under Cabinet
Max. Connectable Units	22
Operating Temperature	-20C (-4F) to a maximum of +40C (+104F)

Compliance

Safety Listing	cETLus
Location Rating	Dry
Energy Star	Yes
ES Unique ID	ESID-2384706
California Status	California T24 Listed
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------