

Conduit Nipples

Galvanized Steel

Features

- NPT thread
- High corrosion resistance

Applications

- Use to extend a length of threaded Rigid or IMC conduit

Standard Material

- Galvanized steel



1/2"-4" meet UL 6 and ANSI C80.1
Federal Specification WW-C-563

Catalog Number	UPC	Size	Length Inches	Ship Case	Weight/100
6451	31130	1/2"	CLOSE	25	6
6451112	31140	1/2"	1-1/2	25	8
64512	31150	1/2"	2	25	12
6451212	31160	1/2"	2-1/2	25	15
64513	31170	1/2"	3	25	26
6451312	31180	1/2"	3-1/2	25	6
64514	31190	1/2"	4	25	26
64515	31200	1/2"	5	25	33
64516	31210	1/2"	6	25	40
64518	31220	1/2"	8	25	54
645110	31230	1/2"	10	25	61
645112	31240	1/2"	12	25	65
6452	31250	3/4"	CLOSE	25	9
6452112	31251	3/4"	1-1/2	25	10
64522	31260	3/4"	2	25	14
6452212	31270	3/4"	2-1/2	25	19
64523	31280	3/4"	3	25	26
6452312	31290	3/4"	3-1/2	25	28
64524	31300	3/4"	4	25	34
64525	31310	3/4"	5	25	43
64526	31320	3/4"	6	25	52
64528	31330	3/4"	8	25	54
645210	31340	3/4"	10	25	56
645212	31350	3/4"	12	25	58

Catalog Number	UPC	Size	Length Inches	Ship Case	Weight/100
6453	31360	1"	CLOSE	25	16
64532	31370	1"	2	25	22
6453212	31380	1"	2-1/2	25	28
64533	31390	1"	3	25	26
6453312	31400	1"	3-1/2	25	43
64534	31410	1"	4	25	49
64535	31420	1"	5	25	64
64536	31430	1"	6	25	20
64538	31440	1"	8	25	25
645310	31450	1"	10	25	25
645312	31460	1"	12	25	25
6454	31470	1-1/4"	CLOSE	25	22
64542	31480	1-1/4"	2	25	28
6454212	31490	1-1/4"	2-1/2	25	37
64543	31500	1-1/4"	3	25	25
6454312	31510	1-1/4"	3-1/2	25	55
64544	31520	1-1/4"	4	25	66
64545	31530	1-1/4"	5	25	84
64546	31540	1-1/4"	6	25	25
64548	31550	1-1/4"	8	25	25
645410	31560	1-1/4"	10	1	2
645412	31570	1-1/4"	12	1	2

Continued on page 2



1/2"-4" meet UL 6 and ANSI C80.1
Federal Specification WW-C-563

Conduit Nipples

Galvanized Steel

Catalog Number	UPC	Size	Length Inches	Ship Case	Weight/100
6455	31580	1-1/2"	CLOSE	25	28
64552	31590	1-1/2"	2	25	34
6455212	31600	1-1/2"	2-1/2	25	44
64553	31610	1-1/2"	3	25	25
6455312	31620	1-1/2"	3-1/2	25	68
64554	31630	1-1/2"	4	25	80
64555	31640	1-1/2"	5	25	103
64556	31650	1-1/2"	6	1	31
64558	31660	1-1/2"	8	1	2
645510	31670	1-1/2"	10	1	2
645512	31680	1-1/2"	12	1	3
6456	31690	2"	CLOSE	25	44
6456212	31700	2"	2-1/2	25	15
64563	31710	2"	3	25	25
6456312	31720	2"	3-1/2	1	40
64564	31730	2"	4	1	40
64565	31740	2"	5	1	44
64566	31750	2"	6	1	46
64567	86336	2"	7	1	25
64568	31760	2"	8	1	2
645610	31770	2"	10	1	3
645612	31780	2"	12	1	3

Catalog Number	UPC	Size	Length Inches	Ship Case	Weight/100
6457	31790	2-1/2"	CLOSE	1	84
64573	31800	2-1/2"	3	1	1
6457312	31810	2-1/2"	3-1/2	1	12
64574	31820	2-1/2"	4	1	150
64575	31830	2-1/2"	5	1	197
64576	31840	2-1/2"	6	1	3
64578	31850	2-1/2"	8	1	3
645710	31860	2-1/2"	10	1	4
645712	31870	2-1/2"	12	1	5
6458	31880	3"	CLOSE	1	1
64583	31890	3"	3	1	1
6458312	31900	3"	3-1/2	1	2
64584	31910	3"	4	1	2
64585	31920	3"	5	1	3
64586	31930	3"	6	1	3
64588	31940	3"	8	1	4
645810	31950	3"	10	1	5
645812	31960	3"	12	1	6
6459	31970	3-1/2"	CLOSE	1	2
64594	31980	3-1/2"	4	1	2
64595	31990	3-1/2"	5	1	3
64596	32000	3-1/2"	6	1	4
64598	32010	3-1/2"	8	1	5
645910	32020	3-1/2"	10	1	7
645912	32030	3-1/2"	12	1	8
6410	32040	4"	CLOSE	1	2
64104	32050	4"	4	1	3
64105	32060	4"	5	1	4
64106	32070	4"	6	1	4
64108	32080	4"	8	1	6
641010	32090	4"	10	1	8
641012	32100	4"	12	1	9