

Project Name

Location

Prepared By



NUVO 65-219

LED DUAL HEAD SECURITY LIGHT

Notes

[www] 10-11-2021 02:00:29

General

Status	Active
Fixture Type	Security Lighting
Finish	Bronze
Wattage	20W
Lumen Output	1900L
CCT (Kelvin)	4000
Temperature	Cool White
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

Specifications

Technology	LED
CRI	80
Voltage	120V
Beam Angle	50
Rated Hours	50000
Operating Temperature	-30C (-22F) to a maximum of +50C (+122F)
Dimmable	Non-Dimmable
Photocell	Has Motion Sensor
Lens Material	Glass
Weight (lb.)	2.8
Material	Die Cast Aluminum

Dimensions

Width (in.)	4.16
Length (in.)	7.63

Compliance

Safety Listing	cULus
Location Rating	Wet
UL Application	Outdoor
Energy Star	Yes
ES Unique ID	ESID-2336405
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------