


ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685





65220 Security Light W/O Sensor Black 4000K *Satco*

Catalog Number	65220
Manufacturer	Satco
Description	Led Security Light - Dual Head Black Finish 4000K
Weight per unit	2.5 (lbs/each)
	Security Lights
Features	
amperage rating	0.200 to 0.072
	Self

uniperagerating	0.200 to 0.072
Ballast Type	Self
Lamp Type	LED
Material	Die Cast Aluminum
Number of Lamps	2
Dowor Dating	0.9
Reflector Type	Frost
Socket Type	
Voltage Rating	120 to 277
Warranty	5 Year Limited - Fixtures
Wattage	20

Material, Color, and Finish

fixture material	die-cast aluminum
Style	Utility

Dimensions and Weight

Height	7.63
Length	7.63
Size	L:7.63 W:4.16 H:4.13
Width	4.16

Descriptions

Description	SECURITY LIGHT W/O SENSOR BLACK 4000K
extra long description	SATCO 65/220 LED DUAL HEAD SECURITY
Long Description	LED Security Light - Dual Head Black Finish 4000K
Product Type	Led Dual Head Security Light
Special Features	Warranty: 5-Years ; FCC Compliant: True ; Cct Selectable: False ;
	CCT (Kelvin Temp): 4000K; Hours Rated: 50000; Beam Angle
	(degree): 50; Indoor Outdoor: Outdoor; IP Rating: IP65; Lens
	Finish: Frost; Lens Material: Glass; Operating Temp: -30C (-22F)
	to +50C (+122F); Watts: 20W; Lumens: 1900L



Type

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

м	١.	_		4	c _	_ 1				c _					
ľ	۱,	12	n	111		CI		·Δr	' In	ГЛ	rr	ทว	1	n	n
	v			u	а	L - I	u	C-1	'In	W		110		w	

Brand	Nuvo	
GTIN	00045923680427	
Manufacturers Part Number	65/220	
UPC	045923680427	

Taxonomies, Classifications, and Categories

Packaging		
Carton	1	
Weight	2.54	
Weight Per each	2.54	

Commercial LED

Uses, Certifications, and Standards

Application	Outdoor
environmental conditions	Wet
Frequency Rating	50/60
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
standard	cULus - Certified