



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



655 2" STL Conn - Concrete Tight

Cooper Crouse-Hinds

Catalog Number	655
Manufacturer	Cooper Crouse-Hinds
Description	Emt Compression Connector, 2 In Trade Size, Straight Connection Orientation, Zinc Plated, Non-Insulated, 2.27 In Length, 2.75 In Diameter, 0.84 In Thread Length, 0.55 LB/Ea
Weight per unit	0.5500 (lbs/each)
Product Category	Steel Uninsulated Straight Com

Features

Material	Steel IN
----------	----------

Material, Color, and Finish

Finish	Zinc Plated
--------	-------------

Dimensions and Weight

Size	2 In IN
------	---------

Descriptions

Description	2" STL CONN - CONCRETE TIGHT
-------------	------------------------------

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00784564106551
UPC	784564106551

Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	Compression Connector, Non-Insulated

Packaging

Carton	5
Weight Per each	0.55

Uses, Certifications, and Standards

standard	UL, cUL
----------	---------

Thin Wall Conduit Fittings (for EMT Conduit)

Compression Type Fittings – Steel

COMPRESSION TYPE FITTINGS – STEEL

Applications:

Thin wall conduit fittings are used:

- To join EMT to a box or enclosure
- To couple two ends of EMT conduit

Features:

- Compression type
- Threadless
- Male hub threads – NPSM
- Steel locknuts
- Heavy steel walls
- Standard material: steel
- Standard finish: zinc plated

Concrete Tight Straight Connectors – Insulated

UL File No. E-22132



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
1650	1/2"	50	11
1651	3/4"	25	16
1652	1"	25	25
1653	1 1/2"	10	43
1654	1 1/2"	10	54
1655	2"	5	76
1656	2 1/2"	2	190
1657	3"	1	300
1658	3 1/2"	1	330
1659	4"	1	360

Straight Connectors – Non-insulated

UL File No. E-22132



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
650S	1/2"	50	9
651S	3/4"	25	16
652	1"	25	25
653	1 1/4"	10	43
654	1 1/2"	10	54
655	2"	5	76
656	2 1/2"	2	190
657	3"	1	300
658	3 1/2"	1	280
659	4"	1	360

Couplings

UL File No. E-22132



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
660S	1/2"	50	12
661S	3/4"	25	18
662	1"	25	27
663	1 1/4"	10	46
664	1 1/2"	10	63
665	2"	5	92
666	2 1/2"	2	250
667	3"	1	410
668	3 1/2"	1	390
669	4"	1	485

EMT Fittings

Available in 7 Colors

Crouse-Hinds series painted EMT fittings consists of set screw, compression, insulated and non-insulated EMT fittings. Although red is the most commonly used, other colors offered include white, blue, green, yellow, black, and orange. These can also be used in architectural design, to better match look and feel to suit architectural specification and preference.



Part Number Example:

650SGreen

Non-insulated Straight Connector		Color
1/2"	650S	Red
3/4"	651S	White
1"	652	Blue
1 1/4"	653	Yellow
1 1/2"	654	Orange
2"	655	Green
2 1/2"	656	Black
3"	657	
3 1/2"	658	
4"	659	

To order, simply add the name of the color needed after the catalog number.