

Stylus Reach® Alkaline Battery-Powered Pen Light

Case Material: Machined aluminum case comes with non-slip grip in black or silver. Flexible cable insulated with PVC.

Dimensions: Reach Length: 14"; 35.5 cm (extended) 6.75"; 17.15 cm (folded) Diameter: .375; .95 cm

Weight: 1.7 oz*; 48g*

Light Source: High-intensity 100,000 hrs LED; available in Arctic White

Light Output: 10 lumens (Arctic White LED)

On/Off: Features a momentary blink switch and constant "on"

Run Time: Up to 60 hours.

Battery: 3 "AAAA" alkaline batteries.

Features:

- Cable allows for 14 inches/35.5 cm of reach
- Waterproof
- Individually serialized
- Pocket clip

Approvals**:

- UL Classified: Intrinsic Safety for Hazardous Locations; Class I, Div.1, Groups A,B,C,D, T3C "Classified" (applies only to Black case)
- UL Classified: Intrinsic Safety for Hazardous Locations; Class I, Div.1, Groups A,B,C,D, T3C; "Exia" (applies only to Black case)
- Most models meet applicable European Community Directives.
- ATEX: II 1G EEx ia IIB T1; DEMKO 04 ATEX 0410949 (applies only to Black case)

Warranty: Limited lifetime warranty.



*With battery (included in purchase).

**See product for specific ratings.



Item		UPC	Part #
<i>English packaging</i>			
Stylus Reach	Black with White LED	080926-65618-5	65618
Stylus Reach UL Listed	Black with White LED	080926-65658-1	65658
Stylus Reach	Silver with White LED	080926-65612-3	65612
<i>Multilingual packaging</i>			
Stylus Reach	Black with White LED	080926-65618-5	65618
Stylus Reach	Black with White LED (ATEX)	080926-65682-6	65682
Stylus Reach	Silver with White LED	080926-65712-0	65712
AAAA Batteries – 6 pack		080926-65030-5	65030

