

Project Name

Location

Prepared By



Notes

[www] 03-22-2021 04:50:54

General

Status	Active
Fixture Type	Wall Pack
Finish	Bronze
Wattage	40
Lumen Output	4200L - 5000L
CCT (Kelvin)	3000K/4000K/5000K
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

Specifications

Technology	LED
CRI	>70
Voltage	120V-277V
Beam Angle	80
Rated Hours	50000
Operating Temperature	-40C (-40F) to a maximum of +45C (+113F)
Dimmable	Non-Dimmable
Photocell	Yes - Bypassable
Surge Protection	Built-in surge protection - 2.5KV
Weight (lb.)	5.08
Material	ADC12 and PC

Dimensions

Height (in.)	8.44
Width (in.)	8.50
Extension (in.)	7.45

Compliance

Safety Listing	cULus
Location Rating	Wet
DLC Approved	Yes
DLC ID	PL23HJ5W5EK3
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes

Additional Information

Additional Information	IK10 Lens
Warranty	5 Year Limited - Fixtures