

Project Name

Location

Prepared By



Notes

[www] 02-09-2021 10:35:53

General

Status	Active
Fixture Type	Strip Light
Finish	White
Wattage	30W/40W/50W
Lumen Output	3900L - 6750L
CCT (Kelvin)	3500K/4000K/5000K
IP Rating	IP20
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
CRI	80
Voltage	100V-277V
Beam Angle	120
Rated Hours	50000
Operating Temperature	-20C (-4F) to a maximum of +60C (+140F)
Dimmable	0-10V Dimming Only
Surge Protection	Built-in surge protection - 2KV
Weight (lb.)	6.84

Dimensions

Height (in.)	3.27
Width (in.)	2.95
Length (in.)	96.00

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PLIHZ3V2CRB9
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------