

Project Name

Location

Prepared By



**Notes**

(www) 18-17-0025 03-20-07

**General**

Status	Active
Fixture Type	Security Lighting
Finish	Black
Wattage	20W
Lumen Output	1900L
CCT (Kelvin)	3000K
Temperature	Warm White
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

**Specifications**

Technology	LED
CRI	80+
Voltage	120V-277V
Beam Angle	50
Rated Hours	50000
Operating Temperature	-30C (-22F) to +50C (+122F)
Dimmable	Non-Dimmable
Photocell or Sensor	No Photocell
Lens Material	Glass
Surge Protection	Built-in surge protection - 2KV
Weight (lb.)	2.41
Material	Die-Cast Aluminum

**Dimensions**

Height (in.)	4.54
Width (in.)	8.16
Extension (in.)	8.8

**Compliance**

Safety Listing	cETLus - Listed
Location Rating	Wet
ENERGY STAR	No
DLC Approved	No
ADA Compliant	No
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
Canadian Standard ICES-005	Class A
SDS Sheet	LED_Fixture

**Additional Information**

Specification Note	Adjustable Angle from 0 to 90 degrees
Warranty	5-Years