

Project Name

Location

Prepared By



NUVO 65-717

LED 2 BULLET HEAD SECURITY LGT

Notes

[www] 03-22-2021 04:30:54

General

Status	Active
Fixture Type	Security Lighting
Finish	White
Wattage	20
Lumen Output	1900
CCT (Kelvin)	4000
Temperature	Cool White
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

Specifications

Technology	LED
CRI	80
Voltage	120V
Beam Angle	50
Rated Hours	50000
Operating Temperature	-30C (-22F) to a maximum of +50C (+122F)
Dimmable	Non-Dimmable
Photocell	Yes
Lens Material	Glass
Surge Protection	Built-in surge protection - 2KV
Weight (lb.)	2.66
Material	Die-Cast Aluminum

Dimensions

Height (in.)	6.42
Width (in.)	8.16
Extension (in.)	8.80

Compliance

Safety Listing	cETLus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2367479
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------