



**65-901**

**BULLET SEC LGT W/ CAMERA - BK**

**GENERAL SPECIFICATIONS**

Fixture Type:	Security Camera
Finish:	Black
Wattage:	20W
Lumen Output:	1900LL
Material:	Metal
IP Rating:	IP65



**TECHNICAL SPECIFICATIONS**

Technology:	LED
Wattage:	20W
Lumen Output:	1900L
Color Temperature:	3000K
CRI:	80CRI
Voltage:	120V-240V
Beam Angle:	50D
Operating Temperature:	-20C (-4F) to a maximum of +60C (+140F)
Dimmable:	Yes-Dimmable
Dimming Function:	Dimmable Only with Starfish App; Dimming range from 100 to less than or equal to 20 percent depending on dimmer control
Weight:	2.78
IP Rating:	IP65

**DIMENSIONS**

Height:	8.46"
Width:	8.27"
Extension:	9.45"

**PACKAGING**

Each UPC:	045923659690
Each Quantity:	1
Each Dimensions:	8.58 x 8.07 x 9.69"
Case UPC:	10045923659697
Case Quantity:	5
Case Dimensions:	41.34 x 9.17 x 10.32"

110 Heartland Blvd.  
Brentwood, NY 11717  
PH 631-243-2022  
FX 631-243-2027

Distribution Centers  
New York, Florida,  
Texas, Washington,  
California, Puerto Rico

National Toll-Free  
800-43-SATCO  
(800-437-2826)  
www.satco.com

Copyright 2022  
Satco Products, Inc.  
All Rights Reserved  
June 13, 2022