

Project Name

Location

Prepared By



NUVO 65-902

BULLET SEC LGT W/ CAMERA - BR

Notes

[www] 06-22-2022 00:35:11

General

Status	Active
Finish	Brown
Wattage	20W
Style	Utility
CCT (Kelvin)	3000K
Color Temperature	Warm White
Width (in.)	8.27
Height (in.)	8.46
Extension (in.)	9.45
Indoor or Outdoor Fixture	Outdoor

Smart Product Info

IOT Enabled	Yes
Integrated Camera	Yes
Operational Humidity	20% to 85% non-condensing
Communication Protocol	802.11b/g/n; WPA/WPA2; WPA-PSK/WPA2-PSK
Voice Assistants Supported	Siri; Alexa; Hey Google; SmartThings
Software Supported	Cloud Storage
Storage Capacity	Micro SD Card to 128GB

Specifications

Technology	LED
CRI	80
Lumen Output	1900L
Rated Hours	50000
Voltage	120V-277V
Dimmable	Yes-Dimmable
Dimming Note	Dimmable Only with Starfish App
Beam Angle	50
Operating Temperature	-20C (-4F) to +60C (+140F)
Weight (lb.)	2.78
Sloped Ceiling	No
Fixture Material	Metal
Fixture Type	Security Camera

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
Energy Star	Pending
CA T20 / T24 Rationale	California T24 2016 & 2019 JA8 Compliant - Outdoor LED
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Compliant
California Prop 65	Lead
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Installation Notes	Must be wired to recessed junction boxes ONLY.
Warranty	5 Year Limited

