



**Product Number:** 15292

**Order Abbreviation:** 65BR/FL 130V

**General Description:** Incandescent BR40 Reflector Lamp Inside Frost Finish 65 Watt 130 Volt

**\* Full Case Required**

#### Product Information

Abbrev. With Packaging Info.	65BRFL130V 24/CS 1/SKU
Approx. Lumens	540
Average Rated Life (hr)	2000
Base	Medium
Beam Angle (deg)	60
Beam Type	WFL
Bulb	BR40
Centerbeam Candlepower (cp)	460
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	5.000
Diameter (mm)	127.00
Filament	CC-6
Lamp Finish	Flood
Maximum Overall Length - MOL (in)	6.500
Maximum Overall Length - MOL (mm)	165.1
Nominal Voltage (V)	130.00
Nominal Wattage (W)	65.00



**Product Number:** 15292

**Order Abbreviation:** 65BR/FL 130V

**General Description:** Incandescent BR40 Reflector Lamp Inside Frost Finish 65 Watt 130 Volt

**\* Full Case Required**

#### Product Information

Abbrev. With Packaging Info.	65BRFL130V 24/CS 1/SKU
Approx. Lumens	540
Average Rated Life (hr)	2000
Base	Medium
Beam Angle (deg)	60
Beam Type	WFL
Bulb	BR40
Centerbeam Candlepower (cp)	460
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	5.000
Diameter (mm)	127.00
Filament	CC-6
Lamp Finish	Flood
Maximum Overall Length - MOL (in)	6.500
Maximum Overall Length - MOL (mm)	165.1
Nominal Voltage (V)	130.00
Nominal Wattage (W)	65.00