



TRADEMASTER GROUNDING TOGGLE SWITCH, LIGHT ALMOND

660LAG | Pass & Seymour

FEATURES & BENEFITS

Single Pole Switch in light almond with grounded terminals, is made with a thermoplastic toggle and frame. It has a smooth, quiet toggle action. It is made with high-impact resistant construction. 15 amps, 120 volts.

*Available in bulk packs of 120. Add "U" to end of Catalog Number. Example: 660LAGU

- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Light Almond

Product Series: TradeMaster

Type: Toggle Number Of Poles: 1

Special Features: Self-Grounding

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 111

CSA Standard: Yes

cULus: Yes

cUL Standard: Yes UL Listing No: UL20 UL Standard: Yes UN SPSC: 39121406

DIMENSIONS

Depth (US): 1.090" Height (US): 3.281" Width (US): 1.25"

TECHNICAL INFORMATION

Amps: 15A Volts: 120VAC Volts (AC): 120

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: Trade Agreement Act Compliant