

Eaton 6612 HS

Catalog Number: 6612 HS

Eaton B-Line series wiring trough, 6" height, 12" length, 6" width, HS wireway, Thru holes, 3 top knockouts, 3 bottom knockouts, Hinged cover, NEMA 1, Steel, Hinged, ANSI 61 gray, 16 gauge

General specifications



Product Name	Catalog Number
Eaton B-Line series wiring trough	6612 HS
UPC	Product Length/Depth
782051478013	12 in
Product Height	Product Width
6 in	6 in
Product Weight	Certifications
4.938 lb	CSA C22.2. UL Listed

Material/finish

Material thickness

16 gauge

Finish color

ANSI 61 gray

Model

Closure type

Hinged

Mounting method

Thru holes

Special features

Cover is secured to the body with plated screws

Type

HS wireway

Resources

Catalogs

[EnviroShield Wireway Flyer](#)

Specifications and datasheets

[Eaton Specification Sheet - 6612 HS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)