

Eaton 6612 HSNK

Catalog Number: 6612 HSNK

Eaton B-Line series wireway, 6" height, 12" length, 6" width, HSNK wireway, Thru holes, No knockouts, Hinged cover, NEMA 1, Steel, Hinged, ANSI 61 gray, 16 gauge

General specifications



Product Name	Catalog Number
Eaton B-Line series wireway	6612 HSNK
UPC	Product Length/Depth
782051479065	12 in
Product Height	Product Width
6 in	6 in
Product Weight	Certifications
4.937 lb	CSA C22.2. UL Listed

Material/finish

Material thickness

16 gauge

Finish color

ANSI 61 gray

Model

Closure type

Hinged

Mounting method

Thru holes

Special features

Cover is secured to the body with plated screws

Type

HSNK wireway

Resources

Catalogs

[EnviroShield Wireway Flyer](#)

Specifications and datasheets

[Eaton Specification Sheet - 6612 HSNK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)