

4 in. x 2 in. Handy Box, Drawn, 1-7/8 in. Deep, Seven 3/4 in. KO's, Raised Ground

By Raco Catalog # 663

4 in. x 2 in. Handy Box, Drawn, 1-7/8 in. Deep, Seven 3/4 in. KO's, Raised Ground



- Drawn construction
- 4 in. x 2 in., 1-7/8 in. deep
- 13 cu. in. capacity
- Raised ground screw feature eliminates interference in surface mounting applications
- Supplied with seven 3/4 in. knockouts
- 13.0 cu. in. capacity
- · Acceptable for use in 2-hour fire rated walls

General

Bracket Type No Bracket
Drawn or Welded Drawn

EU RoHS Indicator Contact Manufacturer

Fire Resistance Yes
Knockouts 3/4 in
Material Steel
Type Box

UPC 050169906637

Wiring System Conduit



Dimensions

Actual Depth	1.875 in
Cubic Capacity	13 cu.in
Depth	1.875 in
Height	4 in
Raised Ground	Yes
Weight	0.473 lb
Width	2.125 in

Certifications And Compliance

Certified Listed UL Listed

Logistics

Carton Quantity 50

Packaging Type No Packaging

Pallet Quantity 4000

Product Assets

Catalogs - RACO / TayMac / Bell Full Catalog

Certifications - UL COC - E195978-18 Certifications - LEED Statement Certifications - NEMA OS1

Sales Drawings - 663

Sales Drawings - RACO-drawn-steel-box-infographic

SDS - HCC_SDS

Terms and Conditions - HCC Terms & Conditions

