



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449



6636G 6X6X36 SC Wireway *Unity Manufacturing*

Catalog Number	6636G
Manufacturer	Unity Manufacturing
Description	Unity 6636G Lay-In Wireway, Removable Hinged Cover Type, Length: 36 In, Width: 6 In, 6 In Height, Nema 1, IP30 Enclosure, Construction: Formed From Code Gauge, Low Carbon Steel, 16 Ga Low Carbon Steel, Gunsmoke Gray Powder Coated, Yes Knockouts, C/Us UI 50 and UI 870 - Type 1: Intended For Indoor Use Primarily to Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, Csa C22.2 No. 26 Certified, Type 1, IEC 60529, Rohs Compliant, For Cable and Wire Junction, Distribution and Termination, Ho
Weight per unit	15.0 (lbs/each)
Product Category	Nema Type 1 Wireway & Fittings

Features

Cover Type	Removable Hinged
Knockouts	Yes
Material	Low-Carbon Steel

Material, Color, and Finish

Finish	Powder Coat
--------	-------------

Dimensions and Weight

Height	6
Length	36
Width	6



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449

Descriptions

Construction	Formed From Code Gauge, Low Carbon Steel
Description	6X6X36 SC WIREWAY
extra long description	UNT 6636G N1 HINGED COVER WIREWAY W
Long Description	Unity 6636G Lay-In Wireway, Removable Hinged Cover Type, Length: 36 IN, Width: 6 IN, 6 IN Height, NEMA 1, IP30 Enclosure, Construction: Formed From Code Gauge, Low Carbon Steel, 16 GA Low Carbon Steel, Gunsmoke Gray Powder Coated, Yes Knockouts, C/US UL 50 And UL 870 - Type 1: Intended For Indoor Use Primarily To Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, CSA C22.2 No. 26 Certified, Type 1, IEC 60529, RoHS Compliant, For Cable And Wire Junction, Distribution And Termination, Ho
Product Type	N1 Hinged Cover Wireway With K.O. Powder Coated
Special Features	For protecting electrical wiring where dust, dirt, oil and water are not serious problems; All sections and fittings are fully open on one side so wires and cables can be laid in along an entire run; No pulling-through of wires or cables is required; Wireway body has mounting holes on the back; Cover is secured to the body with plated screws; Keyhole slots are furnished on the wireway cover which allow easy access to the inside without removing the screws; 1/2 IN, 3/4 IN, 1 IN, 1-1/4 IN Concentric Knockout

Manufacturer Information

Brand	Unity
GTIN	00761515102701
Manufacturers Part Number	6636G
UPC	761515102701

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Lay-In Wireway

Packaging

Carton	1
Package	2
Weight Per each	15



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449

Uses, Certifications, and Standards

Application

For Cable And Wire Junction, Distribution And Termination,
Houses Runs Of Control And Power Cable

Enclosure
standard

NEMA 1, IP30

C/US UL 50 And UL 870 - Type 1: Intended For Indoor Use
Primarily To Provide A Degree Of Protection Against Limited
Amounts Of Falling Dirt, CSA C22.2 No. 26 Certified, Type 1, IEC
60529, RoHS Compliant