Eaton 664-4XSCHC

Catalog Number: 664-4XSCHC

Eaton B-Line series JIC panel enclosure, 6" height, 4" length, 6" width, NEMA 4X, Hinged cover, 4XSCHC enclosure, Wall mount, Small single door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket

General specifications

782051702842

Product Height

Product Weight

6 in

3.9 lb

 Product Name
 Catalog Number

 Eaton B-Line series JIC panel enclosure
 664-4XSCHC

 UPC
 Product Length/E

Product Length/Depth 4 in Product Width 6 in Certifications UL 50

CSA C22.2. NEMA



Photo is representative



Material/finish

Material

304 stainless steel

Wall thickness

16 gauge

Finish color

#4 brushed

Color

Gray

Model

Style Small single door

Model 4XSCHC enclosure

Cover type

Hinged

Mounting method

Wall

Mounting hole details External mounting feet

Closure type Hinged

Special features

Cont. piano hinge,panel mount prov.,s.s.doorclamps

Standards

NEMA Rating 4X Country of origin US

Resources

Catalogs Electrical Enclosure Catalog

Specifications and datasheets Eaton Specification Sheet - 664-4XSCHC



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Righ Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia