

BREAN

SPECIFICATION SHEET

WALL **CONTROLS**





Model 57V (Ivory), 57W (White) Electronic Variable Speed Control (3 Amp)

- Rotary dial for variable selection of fan speed and sound level
- Positive off position
- Fits single-gang box
- Built-in radio noise suppressor
- 120 VAC, 3.0 Amp capacity
- For use with all Broan fans within Amp rating except ceiling paddle fans
- Do not use with impedance protected motor




Model 59V (Ivory), 59W (White) 60-Minute Time Control

- Operates continuously or for any set period up to 60 minutes
- Fits single-gang box
 120 VAC, 20 Amp or 240 VAC, 10 Amp capacity
- Also recommended for low voltage (30V Max)
- For use with all Broan fans and heaters within Amp rating



Model 61V (Ivory), 61W (White) 15-Minute Time Control


- Operates for any set period up to 15 minutes (no "continuous on" position)
- Fits single-gang box 120 VAC, 20 Amp or 240 VAC, 10 Amp capacity
- Also recommended for low voltage (30V Max) applications
- For use with all Broan fans and heaters within Amp rating



Model 62V (Ivory), 62W (White) 60-Minute Time Control

with Two Rocker Switches

- Two, independent, 120 VAC, 15 Amp rocker switches (20 Amp Total)
- Timer operates continuously or for any set period up to 60 minutes
- Fits two-gang box
- 120 VAC, 20 Amp or 240 VAC, 10 Amp timer capacity
- For use with all Broan fans and heaters within Amp rating



Model 63V (Ivory), 63W (White) 60-Minute Time Control with Rocker Switch

- One, independent 120 VAC, 15 Amp rocker switch
- Timer has same features as Model
- For use with all Broan fans and heaters within Amp rating



Model 64V (Ivory), 64W (White) Fan/Light Control with Off-Delay

- Fan and light operate together when control is turned on. Fan continues to operate for a set time period (user adjustable from 1-60 minutes) after light is turned off
- Center position turns fan and light off immediately Can also be used with a fan only

- Fits single-gang box 120 VAC, 4 Amp (fan) and 4 Amp (light) capacity
- For use with all Broan fans and fan/lights within Amp rating. Requires both sides of the electrical line (hot & neutral) in the switchbox



Model 65V (Ivory), 65W (White) Three-Function Control with Brass Finish **Metal Wall Plate**

Model 66V (Ivory), 66W (White) **Three-Function Control with Plastic Wall Plate**

Model 67V (Ivory), 67W (White) Three-Function Control with Chrome Finish **Metal Wall Plate**

- Three, independent, 120 VAC, 15 Amp rocker switches (20 Amp total)
- Fits single-gang opening
 For use with all Broan fans and heaters within Amp rating




Model 68V (Ivory), 68W (White) Two-Function Control

- Two, independent, 120 VAC, 15 Amp rocker switches (20 Amp total)
- Fits single-gang box
- For use with all Broan fans and heaters within Amp rating


Broan-NuTone LLC Hartford, Wisconsin www.broan.com 800-558-1711

REFERENCE	QTY.	REMARKS	Project	
			Location	
			Architect	
			Engineer	
			Contractor	
			Submitted by Date	



Model 69V (Ivory), 69W (White) Single-Function Control

- Fits single-gang box
 120 VAC, 15 Amp
- For use with all Broan fans within Amp



- Red light indicates power is on
- Specially designed for use with Broan Solitaire® Ultra Silent™ fans
- Fits single-gang box120 VAC, 20 Amp



Model 70TW (White) Wall Thermostat for Fans

- Line voltage thermostat automatically activates the ventilator if house temperature rises above the preset comfort setting
- Fits single-gang box125, 250, 277 VAC; 22 Amp capacity
- For use with all Broan fans



Model 71V (Ivory) 12-Hour Timer

- Operates continuously or for any set period up to 12 hours
- Fits single-gang box
- 120 VAC, 20 Amp or 240 VAC, 10 Amp capacity
- For use with all Broan fans and heaters within Amp rating



Model 72V (Ivory), 72W (White) Electronic Variable Speed Control (6 Amp)


- Rotary dial for variable selection of fan speed and sound level
- Positive on/off action
- Fits single-gang box
- Built-in radio noise suppressor
- Switched wire included for additional use if desired (120 VAC, 6 Amp)
- For use with all Broan fans within Amp rating except ceiling paddle fans
- Do not use with impedance protected motor



- 240 VAC, 6 Amp capacity
- For use with Broan Model L3500EXL LoSone® Select™ Cabinet Ventilator
- Other features same as Model 72V



- Specially designed for use with Broan
- SensAire® and Designer Series fan/lights Separate switches control fan (on/off/auto), light (on/off), and night-light (on/off)
- 120 VAC, Amps each rocker = 15, 15, 5 (20 Amp total)
- Fits single-gang opening
- Includes switch function labels



Model 79V (Ivory), 79W (White) Ceiling Paddle Fan Speed and Light Control

Model 78V (Ivory), 78W (White) Ceiling Paddle Fan Speed Control


• For use with all Broan ceiling paddle fans

Four-position speed selection

- Four-position speed selectionHi-Off-Low light control
- Fits single-gang box

Fits single-gang box120 VAC, 1.5 Amp

- 120 VAC, 1.5 Amp fan control; 300 watt maximum light
- For use with all Broan ceiling paddle fans and light kits




Model 269VL (Ivory), 269WL (White) Two-Function Control with Indicator

- Red light indicates power is on
- Specially designed for use with Broan Solitaire® Ultra Silent™ fans and an auxiliary light source
- Fits two-gang box 120 VAC, 20 Amp lighted switch; 120/240/277 VAC, 15 Amp unlighted switch



Model 685VL (Ivory), 685WL (White) Three-Function Control with Indicator

- Red light indicates power is on
- Specially designed for use with Broan Solitaire® Ultra Silent™ fans /lights
- Fits two-gang box
- 120 VAC, 20 Amp lighted switch; 120 VAC, 15 Amp each unlighted switch (20 Amp total)




Model DH100W **Dehumidistat**

- Fits single-gang box
- Variable setting from 20% to 80% relative humidity
- Dual voltage (24V/120V)
- Usage guide included



Model T24H

- 24 Hour Programmable Timer
- Select ON/OFF times in 30 minute increments
- Manual override slide switch
- Fits single-gang boxClock input: 120 VAC, 60 HZ
- Output contacts: 15 Amp 1875 Watt Resistive 8 Amp Inductive 1350 Watt Tunsten 1/2 HP motor



Model 80L

- **Electronic Speed Control (Internal)**
- Specially designed for use with Broan LoSone Select® ventilators rated at 3 Amps or less
- Metal housing
- 3 A, 120 VAC, 60 Hz



