


# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685





#### 670LAG Combo 2 Switches 1P 20A 120/277V La Pass & Seymour/Legrand

Catalog Number	670LAG
Manufacturer	Pass & Seymour/Legrand
Description	Single-Pole, Double Combination Switch, 20A, 120/277V, White.
Weight per unit	0.2160 (lbs/each)
Product Category	Combination Devices

#### **Features**

itures	
action	(2) SP
actuator	Toggle
amperage rating	20
connection	Side wire
Contact Configuration	N-O
Contact Rating	20 Amp, 120/277 VAC
indoor/outdoor	Indoor
Load Rating	20 A @ 120/277 VAC
Load Type	LED, Incandescent, Universal, CFL, Halogen, Fluorescent, Xenon
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	2.0
operating cycles	30k.0
Poles	1
Switch Type	Toggle
throw type	Single Throw
Voltage	120.0 V
Voltage Rating	0.433212996389892
Wall Plate Included	NO
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	#14 - #10 Awg

# Material, Color, and Finish

Finish Matte

# **Dimensions and Weight**

Size 1.32 L x 0.94 W x 4.06 H



# ELLIOTT ELECTRIC SUPPLY 2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

-						
. 1	es	~ri	ın.	T 1	$\sim$	30
						17
_		<b>U</b> I I		•••	•	-

Description	COMBO 2 SWITCHES 1P 20A 120/277V LA
extra long description	P&S 670LAG COMBO 2 SWITCHES 1P 20A
Features	Combination
Long Description	Single-Pole, Double Combination Switch, 20A, 120/277V, White.
Product Type	Combo 2 Switches 1P 20A 120/277V La
Special Features	Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one. Grounding combination devices meet NEC Requirements.

#### **Manufacturer Information**

Brand	Pass and Seymour	
GTIN	00785007006032	
Manufacturers Part Number	670-LAG	
UPC	785007006032	

#### **Taxonomies, Classifications, and Categories**

Category Description	Residential Switches
Туре	COMBINATION

#### **Trade Size**

Amperag	e	20.0

### **Packaging**

Carton	1	
Package	50	
Weight Per each	0.216	

# Uses, Certifications, and Standards

Application	Residential/Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
Operating Temperature	Maximum continuous +60°C, minimum -30°C
standard	CULUS, UL20