

2AA ProPolymer® LED Alkaline Battery-Powered Flashlight

Case Material: Housing made from high impact super tough nylon offering exceptional durability. Rubber-coated facecap resistant to impact and shock.

Dimensions: Length: 6.3 in. Diameter: Major Diameter: 1.30 in. (3.30 cm)
Body Diameter: 0.89 in. (2.26 cm)

Weight: 3.6 oz (100 grams)*

Lens: Unbreakable polycarbonate lens with scratch resistant coating

Light Source: LED - One (1) 0.5 Watt High-Flux LED, 30,000 hour lifetime in parabolic reflector module.

Light Output: 25 lumens. Parabolic reflector produces a focused beam with optimum peripheral illumination.

On/Off: Push button tail switch

Run Time: Up to 18 hours continuous

Battery: Two (2) "AA" size alkaline batteries

Features:

- O-Ring sealed construction; Impact resistant housing – drop test verified
- Dust and water ingress protected to IP57; in accordance with specification EN60529:1992

Approvals: Most models meet applicable European Community Directives.
AA LED – UL Listed, CUL Listed
Class I, Div 2, Groups A, B, C, D; Class II, Div 2, Groups F, G; Class III
Temperature Code T4

Warranty: Limited lifetime warranty.

**With batteries (included in purchase).*



Item	UPC	Part #
2AA LED with alkaline batteries. Yellow	080926-67201-7	67101
2AA LED with alkaline batteries. Black	080926-67100-3	67100
Rubber Helmet Band	080926-99075-3	99075
Nylon holster	080926-68905-3	68905
Safety Wand Red	080926-74903-0	74903
Safety Wand Yellow	080926-74904-7	74904
Safety Wand I/R	080926-74913-9	74913



STREAMLIGHT

30 Eagleville Road • Eagleville, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax • www.streamlight.com