



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



6802 1/2" Extreme Temp BK Met LT 100' *Southwire Company*

Catalog Number	6802
Manufacturer	Southwire Company
Description	Non-UL Extreme Temperature Liquidtight Flexible Metal Conduit, Type Extreme Temp., 6800 Series, Liquidtight Flexible Metal Conduit. Zinc Coated Galvanized Low Carbon Steel, Thermoplastic Elastomer Rubber Jacket. Color: Black, 1/2 Inch Diameter, 100 Foot Carton
Weight per unit	0.2300 (lbs/each)
Product Category	Flexible Metallic Conduit

Features

Inside Diameter	0.622/0.642
Material	Steel
outside diameter	0.820/0.840

Material, Color, and Finish

Color	Black
Finish	Thermoplastic Elastomer
Jacket Material	Thermoplastic Elastomer

Dimensions and Weight

Length	100
--------	-----

Descriptions

Description	1/2" EXTREME TEMP BK MET LT 100'
extra long description	AFC 6802-30-00 1/2 LIQUID-TUFF EX-T
Features	LIQUID-TUFF™ Non-UL Extreme Temperature Liquidtight, Flexible Metal Conduit designed for use where operation at a high temperature is required. The product is appropriate for continuous use at 150°C (302°F) in a dry location, 70°C in a wet location or oily location. The Liquid-Tuff Extreme Temperature jacket material is halogen-free, meets UL 94HB flammability requirements and has a low temperature brittle point of -60°C (-76°F). The product is designed to be used for specific applications where Underwrite
Long Description	Non-UL Extreme Temperature Liquidtight Flexible Metal Conduit, Type Extreme Temp., 6800 Series, Liquidtight Flexible Metal Conduit. Zinc Coated Galvanized Low Carbon Steel, Thermoplastic Elastomer Rubber Jacket. Color: Black, 1/2 inch Diameter, 100 Foot Carton
Product Type	1/2 Liquid-Tuff Ex-T 100 CTN
Short Description	1/2 LIQUID-TUFF EX-T 100 CTN



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Flexible Conduit
GTIN	00077680176851
Manufacturers Part Number	6802-30-00
UPC	077680176851

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	LFMC

Trade Size

Trade Size	1/2
------------	-----

Packaging

Carton	1
Weight	0.23
Weight Per each	0.23

Uses, Certifications, and Standards

Application	- Superior UV and Ozone resistance - Resists extreme temperatures - Very high operating temperatures - For locations requiring halogen free conduits - Industrial applications - Indoor or outdoor locations - Provides mechanical protection for conductors
Temperature Rating	302