

Eaton AH6808UDAC

Catalog Number: AH6808UDAC

Eaton manual motor controller, #14-10 AWG, 20/30A, Industrial, Wall, 600/250V, Back and side, Maintained contact, Black, Open, Two-pole, -20-65°C, Single-phase, Toggle switch, Copper-alloy terminal, brass screw, Single-throw, Thermoset



General specifications

Product Name	Catalog Number
Eaton manual motor controller	AH6808UDAC
UPC	Product Length/Depth
040893123905	4 in
Product Height	Product Width
12 in	4 in
Product Weight	Compliances
0.2 lb	RoHS Compliant NAFTA
Certifications	
cULus Listed	

Product specifications

Special features

Switch only

Number of positions

2

Switch type

Toggle switch

Phase

Single-phase

Termination style

Back and side wire

Closure type

Maintained

Color

Black

Wiring method

Back and side, spring-loaded screw

Material

Thermoset plastic

Enclosure

Open

Mounting method

Wall

Allowable wire size

#14-10 AWG

Amperage Rating

20/30A

Number Of Poles

Two-pole

Contact type

Maintained

Type

Manual motor controller

Device grade

Industrial

Resources

Catalogs

[Arrow Hart Buyers Guide Section E](#)

Specifications and datasheets

[Eaton Specification Sheet - AH6808UDAC](#)

Throw

Single-throw

Operating temperature

-20 to 65 °C

Terminals

Copper-alloy, brass screw

Voltage rating

600/250V

Application

Industrial



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)