

MODEL 682 DUCTLESS CEILING/WALL FAN



Processes air to eliminate odors where ductwork is impossible.

FEATURES

GRILLE:

- Attractive, self-adjusting grille conceals fan interior
- White, polymeric blends well with any decor
- · Torsion spring grille mounting no tools required

MOTOR:

- · Plug-in, removable motor assembly
- Polymeric impeller

HOUSING:

- Patented snap-in mounting saves time and money
- Mounts easily to framing
- Long-lasting activated charcoal filter easy to replace

Controls designed for use with these products (purchase separately):

- Model 57V (Ivory) / 57W (White) Electronic Variable Speed Control - 3 amp
- Model 69V (Ivory) / 69W (White) Single-Function Control

SPECIFICATIONS

MODEL	VOLTS	AMPS
682	120	1.0



TYPICAL SPECIFICATION


Ventilator shall be Broan Model 682.

Unit shall have steel housing with snap-in mounting system.

Fan to have activated charcoal filter. Motor assembly shall be removable for cleaning and service.

Grille to be self-adjusting and require no tools to install or remove.

Unit shall be U.L. Listed.



Broan-NuTone LLC Hartford, Wisconsin www.broan.com 800-558-1711

REFERENCE	QTY.	REMARKS	Project
			Location
			Architect
			Engineer
			Contractor
			Submitted by Date

70F 99041446C