

Combination Switches

696IG



Single Pole, Three-Way Double Combination Switch, 15 amp 120/277 volts, Ivory.

features & benefits

- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

specifications

General Info

Type: Combination, Double Number Of Poles: 1, 3-way

Listing Agencies/Third Party Information

UL Listing No: 20 UL Standard: Yes UN SPS C: 39121406

Dimensions

Depth U S: 0.94" Height U S: 3.28" Width U S: 1.32"



Technical Information

Amps: 16 Amp Volts: 120/277VAC Volts A C: 120/277

Buy American Act Compliance

Country of Origin: MEXICO Buy American Act Status: Trade Agreement Act Compliant