

701A & 711A SERIES

24 HOUR

IN-WALL TIME SWITCH



SPECIFICATIONS

INPUT VOLTAGE: 125VAC, 60Hz.

WIRE SIZE: #14AWG.

OPERATING TEMPERATURE:
32°F to +104°F (0°C to +40°C).

APPLICATIONS



- Porch or patio
- Doorway
- Pool
- Outdoor security lighting

FEATURES

SCHEDULING: Minimum ON setting is 30 minutes. Dial has 48 captive trippers.

BYPASS SWITCH: Slide switch for ON, OFF, or TIMER (automatic) operation.

VACATION MODE: Set timer OFF with no change of tripper settings.

WIRING: Requires a neutral.

CLOCK FORMAT: AM/PM marked on dial.

WALL PLATE: Supplied with single gang wallplate.

ORDERING INFO

CATALOG NO.	UPC CODE	INPUT SUPPLY (VAC) 60 Hz	COLOR
701A	10113	125	White
701AA	10118	125	Light Almond
711A	10114	125	White



CONTACT RATINGS

TYPE	VOLTAGE	RATING	
		701A SERIES	711A SERIES
General Purpose	125 VAC	20A	15A
Resistive	125 VAC	20A	15A
Tungsten	125 VAC	1500W	1250W
Motor	125 VAC	1 HP	1/2HP

IN-WALL TIMERS