



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

805 South Timberlane Drive
71730-0000, AR El Dorado
Phone: 870-639-6289
Fax: 870-864-8850



7075ST 3/4 In Emt Comp Conn Insul Steel

Appleton/Oz Gedney

| | |
|------------------|---|
| Catalog Number | 7075ST |
| Manufacturer | Appleton/Oz Gedney |
| Description | Features:1 1/32IN Dia X 1 1/4IN Length, 7/16 In Thread Length, Concretetight, Standard:UI 514B, Csa C22.2, Nema FB-1, Size:0.75IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated, Insulation:Insulated Throat, Temperature Rating:90ce |
| Weight per unit | 0.1800 (lbs/each) |
| Product Category | Steel Insulated Straight Compr |

Features

| | |
|----------------|------------------|
| connection | Male NPS Thread |
| Connector Type | Compression |
| insulation | Insulated Throat |
| Material | Steel |

Material, Color, and Finish

| | |
|--------|---------------------|
| Color | Metallic |
| Finish | Zinc Electro Plated |

Dimensions and Weight

| | |
|------|------|
| Size | 0.75 |
|------|------|

Descriptions

| | |
|------------------------|--|
| Description | 3/4 IN EMT COMP CONN INSUL STEEL |
| extra long description | EGS 7075ST 3/4 IN EMT COMP CONN INS |
| Long Description | Features:1 1/32IN Dia X 1 1/4IN Length, 7/16 IN Thread Length, Concretetight, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:0.75IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated,Insulation:Insulated Throat, Temperature Rating:90CE |
| Product Type | 3/4 In Emt Comp Conn Insul Steel |
| Special Features | 1 1/32 IN Dia X 1 1/4 IN Length, 7/16 IN Thread Length, Concretetight |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | APPOZGCOMM |
| GTIN | 00687855873142 |
| Manufacturers Part Number | 7075ST |
| UPC | 687855873142 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

805 South Timberlane Drive
71730-0000, AR El Dorado
Phone: 870-639-6289
Fax: 870-864-8850

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | STEEL EMT FITTINGS |
| Type | EMT Conduit Straight Compression Connector |

Trade Size

| | |
|------------|------|
| Trade Size | 0.75 |
|------------|------|

Packaging

| | |
|-----------------|------|
| Carton | 25 |
| Package | 250 |
| Weight Per each | 0.18 |

Uses, Certifications, and Standards

| | |
|--------------------|---|
| Application | To ground and secure EMT Raceways to boxes and enclosures |
| nema rating | FB-1 |
| standard | UL Standard: 514B; UL Listed: E14815, E14895; CSA Standard: C22.2 No. 18.3, cUL Listed: E14815; CSA Certified: 028507; NEMA: FB-1 |
| Temperature Rating | 90 |