



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7165SW 100' Led String Light

Coleman Cable

Catalog Number	7165SW
Manufacturer	Coleman Cable
Description	Led String Light, String Light Type; 14/3 SJTW Cable Type; UL 1088, Csa Approval; Yes Lamp Included; Led Lamp Type; 78 Watt Lamp Wattage; 120 Volt Lamp Voltage; Robust, Rugged Design; Rohs Compliant; Intensity 8000 Lumen; Color Temperature 5000 Kelvin
Weight per unit	N/A
Product Category	Worklight Lighting

Features

Cable Type	14/3 SJTW
design	Robust, Rugged
Lamp Included	Yes
Lamp Type	LED
Lamp Voltage	120 Volt
Lamp Wattage	78 Watt

Descriptions

Additional Information	RoHS Compliant; Intensity 8000 Lumen; Color Temperature 5000 Kelvin; Color Rendering Index 75; Chain Length 100 Foot; Enclosure Rating IP65; Applicable Standard FCC/ICES
Commodity Description	WORKLIGHT LIGHTING
Description	100' LED STRING LIGHT
extra long description	100 FOOT CABLE TYPE; CSA APPROVAL; YES LAMP INCLUDED; LED LAMP TYPE; 78 WATT LAMP WATTAGE; 120 VOLT LAMP VOLTAGE; ROHS COMPLIANT; CORD TYPE 14/3 AWG SJTW; INTENSITY 8000 LUMEN; NO OF STRINGS DAISY CHAINED 10; INCLUDES 100 FOOT LED STRING LIGHT, INSTALLED INSTRUCTION; APPLICABLE STANDARDS FCC/ICES
Long Description	LED STRING LIGHT, STRING LIGHT TYPE; 14/3 SJTW CABLE TYPE; UL 1088, CSA APPROVAL; YES LAMP INCLUDED; LED LAMP TYPE; 78 WATT LAMP WATTAGE; 120 VOLT LAMP VOLTAGE; ROBUST, RUGGED DESIGN; ROHS COMPLIANT; INTENSITY 8000 LUMEN; COLOR TEMPERATURE 5000 KELVIN
Product Type	Led String Light



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Cables & Cords
GTIN	00029892071653
Manufacturers Part Number	7165SW
UPC	029892071653

Taxonomies, Classifications, and Categories

Type	String Light
------	--------------

Packaging

Carton	1
Package	2
Weight Per each	0

Uses, Certifications, and Standards

Approval	UL 1088, CSA
----------	--------------