



# Core & Coil (71A) MH ~GT~ 450W

## CORE & COIL HID MH BAL 750W M149 5-TAP KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

#### **Product data**

General Information		
ANSI Code	M149	
Lamp Type	750W MH	
Number of Lamps	1 piece/unit	
Circuit Type	SUPER-CWA	
Ballast Type	Magnetic HID	
Base Model	71A6452	
Core Size	4 1/4 x 6 (2 Coil)	
Suitable For Outdoor Use	Yes	
Ignitor Catalog Number	LI573-H5	
Ignitor Temperature Rating	105°C	
Capacitor Value	28 MFD	
Capacitor Catalog Number	7C280S40	
Capacitor Requirements	400V	
Capacitor Temperature Rating	105°C	
Capacitor Diameter/Oval Dimensions	2 in	
Capacitor Height	4.8 in	
Automatic Restart	No	
Operating and Electrical		

120/208/240/277/480 V

Input Frequency	60 Hz
Input Current (Open Circuit)	3.3/2/1.8/1.7/0.8 A
Input Current (Starting)	6.6/3.8/3.3/2.8/1.65 A
Input Current (Short Circuit)	5-7.5/2.9-4.3/2.5-3.8/2.1-3.25/1.25-1.9 V
Secondary Short Circuit Current	5-6 A
Constant Wattage Deviation	10%
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Open Circuit Voltage	355 V
Input Current (Nom)	7/4/3.5/3/1.8 A A
Input Power (Nom)	818 W
Rated Lamp Power	750 W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote	15'
Wiring	


Input Voltage

### Core & Coil (71A) MH ~GT~ 450W


Recommended Fuse Value	20/10/10/8/5 A
Approval and Application	
Open Circuit Voltage Test (Volts)	320-390 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	D/C/D/D/C
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029D

Product Data	
Order product name	CORE & COIL HID MH BAL 750W M149 5-TAP KIT
EAN/UPC - Product	781087057490
Order code	913710640401
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913710640401
Net Weight (Piece)	9.131 kg

#### Dimensional drawing



MH BAL 750W M149 5-TAP KIT





© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2019, March 22 - data subject to change