



# Core & Coil (71A) MH ~GT~ 450W

## CORE & COIL HID MH BAL 1500W M48 QUAD KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

### Product data

General Information	
ANSI Code	M48
Lamp Type	1500W MH
Number of Lamps	1 piece/unit
Circuit Type	CWA
Ballast Type	Magnetic HID
Base Model	71A6772
Core Size	4 1/4 x 6 (2 Coil NB)
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	NA
Ignitor Temperature Rating	NA
Capacitor Value	32 MFD
Capacitor Catalog Number	MD3202100
Capacitor Requirements	525V
Capacitor Temperature Rating	90°C
Capacitor Diameter/Oval Dimensions	2 in
Capacitor Height	3.75 in
Automatic Restart	No
Operating and Electrical	
Input Voltage	120/208/240/277 V


Input Frequency	60 Hz
Input Current (Open Circuit)	5.72/3.29/3.04/2.57 A
Input Current (Starting)	10.8/6.13/5.42/4.72 A
Input Current (Short Circuit)	9.1-13.6/5.22-7.83/4.56-6.84/3.96-5.95 V
Secondary Short Circuit Current	7.29-8.9 A
Constant Wattage Deviation	12%
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Open Circuit Voltage	460 V
Input Current (Nom)	13.4/7.8/6.8/5.9 A A
Input Power (Nom)	1610 W
Rated Lamp Power	1500 W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote	Determined by AWG used
Wiring	

## Core & Coil (71A) MH ~GT~ 450W

Recommended Fuse Value	30/25/20/15 A
<b>Approval and Application</b>	
Open Circuit Voltage Test (Volts)	414-506 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	G/E/E/G
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029G

<b>Product Data</b>	
Order product name	CORE & COIL HID MH BAL 1500W M48 QUAD KIT
EAN/UPC - Product	78108767216
Order code	913700574909
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700574909
Net Weight (Piece)	14.370 kg

### Dimensional drawing



MH BAL 1500W M48 QUAD KIT

Product	C1	C2	A1	A2	A3	B1	B2
CORE & COIL HID MH BAL 1500W M48 QUAD KIT	6.7 in	4.7 in	6 in	5.4 in	4.4 in	4.3 in	3.9 in

